

# 1650KP


"CLASSIC" PUSH-PULL TUBE TYPE
ULTRA-LINEAR POTTED OUTPUT TRANSFORMERS

- · Designed for push-pull tube output circuits.
- Enclosed in a drawn steel case, the transformer is completely potted in epoxy and painted in black powder paint to match our potted power transformers & potted chokes.
- Frequency response 30 Hz. to 30 Khz. at full rated power (+/- 1 db max. ref. 1 Khz) minimum.
- Lead connection is via 10 bottom mounted lugs.
- Includes 40% screen taps for Ultra-Linear operation if desired.
- Typical applications Push-Pull: triode, Ultra-Linear pentode, and tetrode connected audio output.
- Suggested tube types: 6L6GC, 807, 5881, EL34, 6146B, 6550B

ELECTRICAL SPECIFICATIONS	
Characteristic	Typical
Input Impedance	3400 Ohms
Output Impedance	4, 8 & 16 Ohms
Output Power	50 Watts
DCR	
Primary 1 - 5	72.50 Ohms
Secondary 6 - 7	0.290 Ohm
Secondary 8 - 10	0.480 Ohm
Inductance   Impedance	@ 60Hz, 10.0V OC
Primary 1 - 5	29.80H 12.58KOhm
Leakage Inductance	@ 60Hz, 10.0V SC
Primary Blue-Brown	10.32mH
Dielectric Strength	2000Vrms
Temperature Range	-40 To 105°C


LABEL:





Note: The above examples of possible combinations are to help you narrow down the choices of transformers for your favorite tube types. How you operate the tubes (push-pull, push-pull parallel, ultra-linear, class, B+, bias, operating points, etc.) will change optimum plate to plate load impedance. Only a few of the most popular tubes are shown. As more tubes become available we will add them to the list. A tube manual or tube manufacturer's technical data sheets should be consulted first, before making a decision on a proper output transformer.

## **DIMENSIONAL DETAILS:**




### **TEST CONDITIONS**

Measurement Instruments: dScope Series III Audio Analyzer Wayne Kerr 3255B with a 3265B Inductance Analyzer HP 4192a LF Impedance Analyzer Keithley 2010 DVM

\* All graphs input level 27dBu @1.0KHz reference.


### TYPICAL TEST CIRCUIT




<sup>\*\*</sup>The results are typical and are subject to normal manufacturing and electrical tolerances.

www.hammondmfg.com

# 1650KP Frequency Response RS = 3600 Ohms



### 1650KP Phase Shift RS = 3600 Ohms



## 1650KP THD+N RS = 3600 Ohms

