





TOLERANCE UNLESS OTHERWISE SPECIFIED	
.X	±0.15
.XX	±0.10

THIS IS A C.A.D. GENERATED DRAWING  
DO NOT MAKE MANUAL REVISIONS TO MASTER.



ISSUE NUMBER	
ORIGINAL	①



#### SPECIFICATION:

##### MATERIAL:

CONTACT: BRASS, GOLD FLASH PLATING ALL OVER NICKEL UNDERPLATING

HOUSING: PA46, BLACK

MAGNET: N52

##### ELECTRICAL:

RATED VOLTAGE (PER CONTACT): 12V

RATED CURRENT (PER CONTACT): 2A

INSULATION RESISTANCE: 100MEGAOHMS MIN.

DIELECTRIC WITHSTAND VOLTAGE: 100V AT 60Hz

CONTACT RESISTANCE: 30mOHMS MAX. BEFORE TEST AND 60mOHMS MAX. AFTER TEST

MECHANICAL LIFE: 30,000 CYCLES MIN.

WORKING TEMPERATURE RANGE: -30~+85°C



THIS SERIES FULLY CONFORMS TO  
THE EUROPEAN UNION DIRECTIVES  
2011/65/EU FOR RoHS COMPLIANCY.



YOUR CONNECTION TO QUALITY & SERVICE

EDAC INC  
TORONTO, ONTARIO  
CANADA

THESE DRAWINGS AND SPECIFICATIONS  
ARE THE PROPERTY OF EDAC INC., AND  
SHALL NOT BE REPRODUCED, OR COPIED  
OR USED AS THE BASIS FOR THE  
MANUFACTURE OR SALE OF APPARATUS  
WITHOUT WRITTEN PERMISSION.

### MAGNETIC SPRING LOADED CONNECTOR, 3POS, FEMALE

ACAD REFERENCE NO.: 686E0321250110E		UNIT: MM
DRAWN: J.L.	DATE: 3/13/2023	
CHECKED: R.S.M	DATE: 3/13/2023	
SCALE: (IN CAD 1:1)	SHEET 1 OF 1	
DRAWING NUMBER: 686E0321250110E	ISSUE	
PART NUMBER: 686E0321250110E	1	