


6		5		4		3		2		1	
ITEM	PART#	DESCRIPTION		QTY	UOM			FROM	TO	DESCRIPTION	COLOUR
A	5023800400	1.25 W/B Single Plg Hsg 4Ckt		1	PC			A1	--	1X26AWG DISC BK	BLACK
B	5023810000	1.25 W/B Single Plg Term W/Plt		4	PC			A2	--	1X26AWG DISC BK	BLACK
C	--	WHITE PART ID LABEL		1	PC			A3	--	1X26AWG DISC BK	BLACK
								A4	--	1X26AWG DISC BK	BLACK



PART NUMBER	TITLE	L1	L2(REF)
2240921042	CLIK-Mate 1.25 R-S 4ckt 150mm disc Sn	150±5	15
2240921043	CLIK-Mate 1.25 R-S 4ckt 300mm disc Sn	300±5	15
2240921044	CLIK-Mate 1.25 R-S 4ckt 600mm disc Sn	600±5	15

MOLEX P/N
MOLEX
BATCH WK/YR

DETAIL A

NOTES

1. CABLE ASSEMBLY TO BE TESTED 100% FOR CONTINUITY AND POLARITY.
 2. CONNECTOR VIEW SHOWN IS FROM MATING SIDE.
 - 3.LABEL TEXT MUST BE 2 MM MAX. IN HEIGHT WITH ARIAL FONT.
 - 4.LABEL MUST BE WRAPPED IN FLAG TYPE ON A SINGLE CABLE.
 - 5.TINNING SHOULD BE DONE WITH LEAD FREE SOLDER BAR ONLY.
 - 6.FREE ENDS MUST BE STRIPPED,TWISTED & TINNED.
- THE LENGTH OF TINNING IS 5±1 MM.TINNING DIA MUST BE 0.65 MM MAX.

REVISION			
DATE	REV	DESCRIPTION	CHANGER
2023/11/04	C	INITIAL RELEASE	THANUB
DOCUMENT STATUS	P1	RELEASE DATE	2023/05/05 16:46:44

FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	
	DIMENSION UNITS	SCALE
	mm	NTS
	GENERAL TOLERANCES (UNLESS SPECIFIED)	
DIVISIONAL SYMBOLS	ANGULAR TOL	± °
	4 PLACES	±
	3 PLACES	±
	2 PLACES	±
	1 PLACE	±
	0 PLACES	±
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	THIRD ANGLE PROJECTION
	DRAWING	SERIES
		MATERIAL NUMBER
		CUSTOMER
		SHEET NUMBER