


6		5		4		3		2		1	
ITEM	PART#	DESCRIPTION		QTY	UOM						
A	5023800600	1.25 W/B Single Plg Hsg 6Ckt		1	PC						
B	5023810000	1.25 W/B Single Plg Term W/Plt		6	PC						
C	--	WHITE PART ID LABEL		1	PC						

FROM	TO	DESCRIPTION	COLOUR
A1	--	1X26AWG DISC BK	BLACK
A2	--	1X26AWG DISC BK	BLACK
A3	--	1X26AWG DISC BK	BLACK
A4	--	1X26AWG DISC BK	BLACK
A5	--	1X26AWG DISC BK	BLACK
A6	--	1X26AWG DISC BK	BLACK



NOTES

1. CABLE ASSEMBLY TO BE TESTED 100% FOR CONTINUITY AND POLARITY.
 2. CONNECTOR VIEW SHOWN IS FROM MATING SIDE.
 - 3.LABEL TEXT MUST BE 2 MM MAX. IN HEIGHT WITH ARIAL FONT.
 - 4.LABEL MUST BE WRAPPED IN FLAG TYPE ON A SINGLE CABLE.
 - 5.TINNING SHOULD BE DONE WITH LEAD FREE SOLDER BAR ONLY.
 - 6.FREE ENDS MUST BE STRIPPED,TWISTED & TINNED.
- THE LENGTH OF TINNING IS 5±1 MM.TINNING DIA MUST BE 0.65 MM MAX.

REVISION			
DATE	REV	DESCRIPTION	CHANGER
2023/11/04	B	INITIAL RELEASE	THANUB
RELEASE STATUS		P1	RELEASE DATE
			2023/05/05 16:46:44

FUNCTIONAL SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																							
$\frac{F}{A} = 0$		DIMENSION UNITS		SCALE		CURRENT REV DESC:																			
$\frac{F}{E} = 0$		mm		NTS																					
$\frac{F}{P} = 0$		GENERAL TOLERANCES (UNLESS SPECIFIED)																							
		ANGULAR TOL ± °																							
		4 PLACES		±		EC NO: 745876 DRWN: THANUB 2023/04/11 CHK'D: RDOMZALS 2023/05/05 APPR: RDOMZALS 2023/05/05																			
		3 PLACES		±																					
		2 PLACES		±																					
		1 PLACE		±		INITIAL REVISION: DRWN: THANUB 2023/01/15 APPR: SKUMAR07 2023/02/06																			
		0 PLACES		±																					
		DIVISIONAL SYMBOLS				THIRD ANGLE PROJECTION		DRAWING		SERIES															
								A4-SIZE		224092															
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS																							