




COMMENT:
ALL RIGHTS ARE RESERVED BY US FOR THIS DRAWING. WITHOUT OUR PRIOR CONSENT,
IT MAY NEITHER BE DUBLICATED NOR MADE AVAILABLE TO A THIRD PARTY,
AND IT ALSO MAY NOT BE IMPROPERLY USED BY TE RECEIVER, OR A THIRD PARTY.














5 : 1

RoHS compliant
by exemption

Threaded insert 4-40 KL	F52M122M1046	Brass (nonmagnetic)	tin plated
Threaded insert 4-40 KL	F52M122M1000	Brass (nonmagnetic)	blank
Threaded insert 4-40 KL	F52M122M100	Brass	blank
<i>Type Description</i>	<i>Part No.</i>	<i>Material</i>	<i>Surface plating/Colour/Class</i>

MATERIAL NO.	TYPE DESCRIPTION
-	F52M122M100
1731120550	F52M122M100+S
-	F52M122M1000
1731140052	F52M122M1046

SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
 = 0	DIMENSION UNITS mm	SCALE 2:1	MEASUREMENTS WITHOUT TOLERANCE ACC. TO ISO 2768-m					molex					
 = 0			CURRENT REVISION										
 = 0													
 = 0	4	24130	DRWN: DRAWN BY FVetter			15-02-2019		FCT-Threaded insert 4-40 KL					
 = 0	3	23101	APPR: APPR BY MTeubel			15-02-2019							
 = 0	2	22426	INITIAL REVISION										PRODUCT CUSTOMER DRAWING
 = 0	1							DRWN: DRAWN BY Denzinger 09-02-2004 APPR: APPR BY okappla 11-02-2004					
 = 0	REV.	CH.-NO.											see table
 = 0	REPLACEMENT FOR:		THIRD ANGLE PROJECTION		DRAWING		DOCUMENT NUMBER			CUSTOMER		SHEET NUMBER	
 = 0					A4-SIZE		F52M122_D			GENERAL MARKET		1 OF 1	