








注記：
NOTES：

- ① 材質及び仕上げ(めっき仕様)：TABLE 1参照
MATERIAL AND FINISHES (PLATING SPECIFICATION)：SEE TABLE 1
- ② 製品仕様書、コネクタ取扱説明書、適合嵌合相手はSHEET 3をご参照ください。
PLEASE REFER TO SHEET 3 FOR PRODUCT SPECIFICATION,
APPLICATION SPECIFICATION AND MATE WITH.
- ③ 偶数極に適用
APPLY TO EVEN CIRCUIT
- ④ 発注番号：SHEET 3 参照
ORDER NUMBER：PLEASE REFER TO SHEET 3

220098**7*

極数
CIRCUIT SIZE


NO.	ハウジングカラー HOUSING COLOR
0	ナチュラル(白) NATURAL (WHITE)
1	黒 BLACK

-	22	18.75	21.9	16
-	20.75	17.5	20.65	15
-	19.5	16.25	19.4	14
-	18.25	15	18.15	13
-	17	13.75	16.9	12
-	15.75	12.5	15.65	11
-	14.5	11.25	14.4	10
14.45	13.25	10	13.15	9
13.2	12	8.75	11.9	8
11.95	10.75	7.5	10.65	7
10.7	9.5	6.25	9.4	6
9.45	8.25	5	8.15	5
8.2	7	3.75	6.9	4
6.95	5.75	2.5	5.65	3
5.7	4.5	1.25	4.4	2
D	C	B	A	極数 CIRCUIT SIZE

① TABLE 1

番号 NO.	部品 PART	材質 MATERIAL
①	ハウジング HOUSING	ポリアミド(PA), ガラス充填, UL94V-0, 色 : SHEET 3参照 POLYAMIDE (PA), GLASS FILLED, UL94V-0, COLOR : SEE SHEET 3
②	ターミナル TERMINAL	黄銅 BRASS
		錫ピスマスめっき : 1.0 MICROMETER MINIMUM TIN-BISMUTH PLATING
		ニッケルめっき (下地めっき) : 1.0 MICROMETER MINIMUM NICKEL PLATING (UNDERPLATING)


① ハウジング
HOUSING




② ターミナル
TERMINAL

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						
DIMENSION UNITS		SCALE		CURRENT REV DESC:		
mm		NTS				
GENERAL TOLERANCES (UNLESS SPECIFIED)				molex		
ANGULAR TOL ± 3.0 °						
4 PLACES		± 0.2		MICRO-LOCK PLUS 1.25 W/B SINGLE ROW RIGHT ANGLE THROUGH HOLE PLUG ASSEMBLY WITH BOSS LOW HALOGEN TIN-BISMUTH PLATING		
3 PLACES		± 0.2				
2 PLACES		± 0.2				
1 PLACE		± 0.2		PRODUCT CUSTOMER DRAWING		
0 PLACES		± 0.2				
EC NO: 757367				DOCUMENT NUMBER		
DRWN: SOKUMURA01 2022/06/21						
CHK'D: SAKIYAMA 2023/09/12						
APPR: AIDA 2023/09/12				DOC TYPE		
INITIAL REVISION:						
DRWN: SOKUMURA01 2022/06/21						
APPR: AIDA 2023/09/12				DOC PART		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS						
THIRD ANGLE PROJECTION						
DRAWING		SERIES		REVISION		
A3-SIZE		220098				
220098		220098				
MATERIAL NUMBER		CUSTOMER		SHEET NUMBER		
SEE SHEET 3		GENERAL				
1 OF 3		1 OF 3				


製品形状
PRODUCT SHAPE




2-11極
2-11 CIRCUIT



12-13極
12-13 CIRCUIT




14極
14 CIRCUIT




15-16極
15-16 CIRCUIT


嵌合状態図
MATED CONNECTORS




嵌合相手 : 204532シリーズ
MATE WITH : 204532 SERIES




嵌合相手 : 214526シリーズ
MATE WITH : 214526 SERIES



リテーナー : 214528シリーズ
RETAINER : 214528 SERIES



推奨基板レイアウト
RECOMMENDED PCB PATTERN LAYOUT



基板取付穴推奨寸法 (t=0.8)
RECOMMENDED PCB HOLE DIMENSION (t=0.8)

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							
DIMENSION UNITS		SCALE		CURRENT REV DESC:			
mm		NTS					
GENERAL TOLERANCES (UNLESS SPECIFIED)				molex			
ANGULAR TOL ± 3.0 °							
4 PLACES ± 0.2		EC NO: 757367		MICRO-LOCK PLUS 1.25 W/B SINGLE ROW RIGHT ANGLE THROUGH HOLE PLUG ASSEMBLY WITH BOSS LOW HALOGEN TIN-BISMUTH PLATING			
3 PLACES ± 0.2		DRWN: SOKUMURA01 2022/06/21					
2 PLACES ± 0.2		CHK'D: SAKIYAMA 2023/09/12					
1 PLACE ± 0.2		APPR: AIDA 2023/09/12		PRODUCT CUSTOMER DRAWING			
0 PLACES ± 0.2		INITIAL REVISION:					
DRWN: SOKUMURA01 2022/06/21				DOCUMENT NUMBER			
APPR: AIDA 2023/09/12				2200980000-SD			
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		DRAWING		DOC TYPE	
				SERIES		DOC PART	
		A3-SIZE		220098		REVISION	
				MATERIAL NUMBER		DOC PART	
				SEE SHEET 3		A	
				CUSTOMER		PSD	
				GENERAL		000	
						SHEET NUMBER	
						2 OF 3	

