


6		5		4	
ITEM	PART#	DESCRIPTION		QTY	UOM
A	2078410005	RECEPTACLE HOUSING FOR L1NK 250 - 1X5 Ck		1	PC
B	466261305	CRIMP TERMINAL FOR L1NK 250 - 22-24 AWG		5	PC
C	--	WHITE PART ID LABEL		1	PC

2		1	
FROM	TO	DESCRIPTION	COLOUR
A1	--	1X22AWG DISC PVC BK UL1569	BLACK
A2	--	1X22AWG DISC PVC BK UL1569	BLACK
A3	--	1X22AWG DISC PVC BK UL1569	BLACK
A4	--	1X22AWG DISC PVC BK UL1569	BLACK
A5	--	1X22AWG DISC PVC BK UL1569	BLACK



PART NUMBER	TITLE	L1	L2(REF)
2240901050	KK Plus250 R-R 5ckt 50mm disc Sn	50±5	15
2240901051	KK Plus250 R-R 5ckt 100mm disc Sn	100±5	15
2240901052	KK Plus250 R-R 5ckt 150mm disc Sn	150±5	15
2240901053	KK Plus250 R-R 5ckt 300mm disc Sn	300±5	15
2240901054	KK Plus250 R-R 5ckt 600mm disc Sn	600±5	15

- NOTES
- 1.THE PRODUCT MUST MEET PERFORMANCE SPECIFICATION AS PER ES-36586-004.
 - 2.CONNECTOR VIEW SHOWN IS FROM MATING SIDE.
 - 3.LABEL TEXT MUST BE 2 MM MAX. IN HEIGHT WITH ARIAL FONT.
 - 4.LABEL MUST BE WRAPPED IN FLAG TYPE ON A SINGLE CABLE.
 - 5.TINNING SHOULD BE DONE WITH LEAD FREE SOLDER BAR ONLY.
 - 6.FREE ENDS MUST BE STRIPPED,TWISTED & TINNED.
 - 7.THE LENGTH OF TINNING IS 5±1 MM.TINNING DIA MUST BE 1.0 MM MAX.

REVISION			
DATE	REV	DESCRIPTION	CHANGER
02/22/2023	B	INITIAL RELEASE	THANUB
RELEASE STATUS		P1	RELEASE DATE
			2023/03/23 11:04:44

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION															
FUNCTIONAL SYMBOLS $\frac{F}{A} = 0$ $\frac{F}{E} = 0$ $\frac{F}{P} = 0$		DIMENSION UNITS		SCALE		CURRENT REV DESC:									
		mm		NTS											
		GENERAL TOLERANCES (UNLESS SPECIFIED)				molex SEE TABLE									
		ANGULAR TOL ± °													
DIVISIONAL SYMBOLS		4 PLACES		±								EC NO: 743463		2023/02/23	
		3 PLACES		±								DRWN: THANUB		2023/03/23	
		2 PLACES		±		CHK'D: SKUMAR07		2023/03/23							
		1 PLACE		±		APPR: SKUMAR07		2023/03/23							
		0 PLACES		±		INITIAL REVISION:									
						DRWN: THANUB		2023/02/20		DOCUMENT NUMBER					
						APPR: SKUMAR07		2023/03/23		2240901050					
										DOC TYPE					
										DOC PART					
										REVISION					
										B					

MOLEX P/N
MOLEX
BATCH WK/YR

DETAIL A