

REV. A	SHEET 1 OF 3	DOCUMENT NO. CF-020400-57X
REVISIONS M		
LTR	DESCRIPTION	DATE
A	INITIAL RELEASE	10/03/2022

CF-020400-57X

SHEET 1 OF 3


REV. A

C

B

A

PART NUMBER	J2 CONNECTOR KEY ROTATION	J3 CONNECTOR KEY ROTATION
CF-020400-57N	N	N



SEE SHEET 3

NOTES:

THE USE OF THIS DOCUMENT IS UNLIMITED.
HOWEVER, DOCUMENTS REFERENCED HEREON
MAY CONTAIN LIMITED RIGHTS DATA.

RELEASED / Oct. 06 2022, 7:55:10 AM

DOCUMENT NO.
CF-020400-57X

SHEET 1 OF 3

REV.
A

PRO/ENGINEER INFORMATION
Pro/e Model Used:
CF-020400-57X.ASSEM
Drawing Name:
CF-020400-57X

NONE

NEXT ASSEMBLY

UNLESS OTHERWISE SPECIFIED	SPECIFICATIONS	POS	QTY	PART NUMBER	DESCRIPTION	NOTE
LINEAR DIMENSIONS ARE IN INCHES TOLERANCES: .XXXX = $\pm .0005$ ANGLES = $\pm 2^\circ$.XXX = $\pm .010$.XX = $\pm .03$.X = $\pm .1$ DIM. & TOL. PER ASME Y14.5M; DRM PER MIL-STD-31000; OTHER Amphenol Stds. PER 9-3800 LEGENDS: = FLAG NOTE CALL OUT REFERENCE ONLY	MATERIAL SPEC.	PARTS LIST				
	NONE	APPROVALS				
	PROCESS SPEC.	THIRD ANGLE PROJECTION				
	SEE NOTE 8	DATE: 29-Sep-22				
		PREPARED BY: W. LEE		AMPHENOL CORPORATION		
		ENGINEER IN CHARGE: W. LEE		40-60 DELAWARE AVENUE SIDNEY, N.Y. 13838		
		DESIGN MANAGER: J. ROTHROCK		ETHERNET SWITCH		
		DESIGN ACTIVITY GROUP: CI		4 PORTS		
				SIZE: C	CAGE CODE: 77820	DOCUMENT NO.: CF-020400-57X
				SCALE: 1:5	REF: CF-020400-51X	SHEET 1 OF 3

REV. A

SHEET 1 OF 3

CF-020400-57X

DOCUMENT NO.

U

4

3

2

REV. A

SHEET 2 OF 3

DOCUMENT NO. CF-020400-57X

DOCUMENT NO. CF-020400-57X

SHEET 2 OF 3

REV. A

J2 CONNECTOR	
ID	DESCRIPTION
1	CHASSIS_GND
2	CHASSIS_GND
3	CHASSIS_GND
4	CHASSIS_GND
5	28VDC
6	28VDC_RTN

J3 CONNECTOR 7		
ID	DESCRIPTION	FIBER TYPE
A	CH_1_1GBASE-LX_TX	9/125 SINGLE-MODE 1310nm
B	CH_1_1GBASE-LX_RX	
C	CH_2_1GBASE-LX_TX	
D	CH_2_1GBASE-LX_RX	50/125 MULTI-MODE 850nm
E	CH_3_1GBASE-SX_TX	
F	CH_3_1GBASE-SX_RX	
G	CH_4_1GBASE-SX_TX	
H	CH_4_1GBASE-SX_RX	

SEE SHEET 3

NOTES:

THE USE OF THIS DOCUMENT IS UNLIMITED.
HOWEVER, DOCUMENTS REFERENCED HEREON
MAY CONTAIN LIMITED RIGHTS DATA.

RELEASED / Oct. 06 2022, 7:55:10 AM

DOCUMENT NO. CF-020400-57X

SHEET 2 OF 3

REV. A

MAIN KEYWAY

CTF-QUAD TOSA
1310nm SINGLE-MODE
CF-170900-044
2 PLACES
CAVITY A,C

CTF-QUAD ROSA
1310nm SINGLE-MODE
CF-170900-045
2 PLACES
CAVITY B,D

CTF-QUAD ROSA
850nm MULTI-MODE
CF-170900-001
CAVITY F,H

CTF-QUAD TOSA
850nm MULTI-MODE
CF-170900-000
CAVITY E,G

DETAIL B

J3 CONNECTOR

SCALE 3.000

13

SIZE C

CAGE CODE 77820

DOCUMENT NO. CF-020400-57X

REV. A

SCALE: 1.5

REF: CF-020400-51X

SHEET 2 OF 3

DOCUMENT NO. CF-020400-57X

SHEET 2 OF 3

REV. A

Eng. PDM Information
For Reference Only

REVISION A

VERSION 1

4

3

2

REV. A

SHEET 3 OF 3

DOCUMENT NO. CF-020400-57X

DOCUMENT NO. CF-020400-57X


SHEET 3 OF 3

REV. A

1

15

17




17

ESD WARNING LABEL

FRONT ISOMETRIC VIEW

SCALE 1.000



REAR ISOMETRIC VIEW

SCALE 1.000

10. APPROXIMATE WEIGHT: 272 GRAMS

9. CONVERTER HOUSING AND CONNECTOR SHELLS ARE Ni-PTFE (DURMALON) PLATED ALUMINUM ALLOY.

8. PROCESS SPEC: 9-3856-5, 9-9172-3

7. SEE J3 CONNECTOR I/O TABLE FOR COMPATIBLE FIBER TYPES.

6. PACKAGE PER PRODUCTION PROCESS SHEET.

5. MARKING DATA MAY DIFFER FROM DRAWING BASED ON CUSTOMER SPECIFIC ORDER REQUIREMENTS.

4. ASSEMBLY CONTAINS ELECTROSTATIC DISCHARGE (ESD) SENSITIVE COMPONENTS. ASSEMBLY SHALL BE HANDLED, PACKAGED, AND SHIPPED TO MEET REQUIREMENTS OF ANSI/ESD-S-20.20 AND IPC-A-610.

3. PROTECTIVE CAPS SHALL BE INSTALLED PRIOR TO SHIPPING.

2. PACKAGE LABEL SHALL CONTAIN THE SAME INFORMATION SHOWN IN NOTE 1.

1. MARK LABEL "AMPHENOL", PART NUMBER AND SEVEN DIGIT SERIAL NUMBER AND ATTACH ON INDICATED SURFACE. SERIAL NUMBER PER 9-9172-3.

EXAMPLE: FOR NORMAL KEY CONVERTER NUMBER 8 BUILT ON AUG 19, 2022

AMPHENOL
CF-020400-57N
2233008

NOTES:

THE USE OF THIS DOCUMENT IS UNLIMITED. HOWEVER, DOCUMENTS REFERENCED HEREON MAY CONTAIN LIMITED RIGHTS DATA.

RELEASED / Oct. 06 2022, 7:55:10 AM

DOCUMENT NO. CF-020400-57X

SHEET 3 OF 3

REV. A

17. BRADY B-103 CLEAR LAMINATING APPLIED TO INDICATED LABEL.

16. OPERATING TEMPERATURE: -40°C TO 70°C
STORAGE TEMPERATURE: -55°C TO 85°C

15. LABEL MATERIAL:
POLYESTER WITH PERMANENT ACRYLIC ADHESIVE
BRADY B-422

14. MATING CONNECTOR REFERENCE:
J2 MATING CONNECTOR: TV06DT-9-35S OR EQUIVALENT
J3 MATING CONNECTOR: TV06QDT-25-8S(LC) OR EQUIVALENT
J3 MATING CONTACT:
CF-198149-128 ARINC801 FOR TIGHT STRUCTURE FIBER
WITH CF-198201-000 ARINC801 ADAPTER

13. FOR INSERT ARRANGEMENT, SEE FOLLOWING DOCUMENTS.
J2 CONNECTOR: L-21808-35
J3 CONNECTOR: LQ-21824-8

12. J2 AND J3 CONNECTOR DESIGNATORS SHALL BE STAMPED IN CONTRASTING COLOR PER 9-3856-5. LOCATION OF DESIGNATORS SHALL BE APPROXIMATELY AS SHOWN. .075" MINIMUM LETTER HEIGHT.

11. USE OF LEAD-FREE SOLDER IS PROHIBITED.

1

2

3

4

REV. A

SHEET 3 OF 3

DOCUMENT NO. CF-020400-57X

SIZE C

CAGE CODE 77820

DOCUMENT NO. CF-020400-57X

REV. A

SCALE: 1.5

REF: CF-020400-51X

SHEET 3 OF 3