








REVISIONS					
REV	ECO	DESCRIPTION	DATE	BY	APPR
A1	--	RELEASED DRAWING	08/AUG/22	RONALD	TOMMY
A2	--	UPDATE THE PRODUCT NAME	27/OCT/22	LUCAS	TOMMY



PART NUMBER CHART	
COLOR	PART NUMBER
BLACK	ATS13-26Px-BM01
GREY	ATS13-26Px-BM01-GY
GREEN	ATS13-26Px-BM01-GN
BROWN	ATS13-26Px-BM01-BN




RECOMMENDED PANEL CUTOUT



NOTES: UNLESS OTHERWISE SPECIFIED

- MATERIAL:
HOUSING: THERMOPLASTIC;
ARRANGEMENT PLATE: THERMOPLASTIC; COLOR:BLACK
CONTACT: COPPER ALLOY,GOLD PLATING
SEAL:SILICONE RUBBER
- SPECIFICATIONS:
2.1 CURRENT RATING: 7.5AMPS MAX
2.2 OPERATING TEMPERATURE: -55°C TO +125°C
2.3 DIELECTRIC WITHSTANDING VOLTAGE: LESS THAN 2 MILLIAMPS CURRENT LEAKAGE @ 1500 VOLTS AC.
2.4 INSULATION RESISTANCE: 1000 MEGOHMS MIN @ 25°C.
2.5 MOISTURE RESISTANCE: IP67&IP69K (MATED CONDITION)
2.6 MATING CYCLE DURABILITY: 500 MIN CYCLES
2.7 RoHS COMPLIANT
- MATING PART: ATS06-26Sx-* PLUG
(x = A,B KEYS ; * = ALL MODIFICATIONS)
- ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.



RECOMMENDED PCB LAYOUT

SEE P/N CHART		REF: 9-6437287-8, 9-6437287-9 (MATING INTERFACE ONLY)	
QUANTITY	PART NUMBER	DESCRIPTION	ITEM
MATERIALS LIST			
UNLESS OTHERWISE SPECIFIED		SIGNATURES	DATE
1) All dimensions are in metric(mm).		DRAWN: LUCAS	27/OCT/22
2) Tolerances are as follows:		CHECKED: ORION	30/OCT/22
1 PL DEC ±0.30		ENGINEER:	
2 PL DEC ±0.15		APPROVAL: TOMMY	31/OCT/22
3 PL DEC ±0.08		CUSTOMER:	
3) Note reference = X		THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.	
MATERIAL SPECIFICATIONS:		WEIGHT: 23.0g	
PROCESS SPECIFICATIONS:		NEXT ASSY:	
SIZE B		TYPE C-	DWG NO: ATS13-26Px-BM01-xx
SCALE: NONE		REVISION A2	
SHEET 1		OF 1	

TITLE: 26 POS, PCB RECEPT W/ FLANGE, PIN, ATS SERIES, PANEL, RIGHT ANGLE

DWG NO:

ATS13-26Px-BM01-xx

REV: A2

SH: 1

OF: 1