

ATS Series™ - Contact Size 20 Options

Machined, Crimp Contacts				
Part Number		Contact Size (AWG)	Wire Range (mm²)	Plating
Male	Female			
MP20W23F	MS20W23F	22-20AWG	0.34-0.50 mm²	Gold Flash
MP20W23G5	MS20W23G5	22-20AWG	0.34-0.50 mm²	Gold 5µ"
MP20W23G10	MS20W23G10	22-20AWG	0.34-0.50 mm²	Gold 10µ"
MP20W23G15	MS20W23G15	22-20AWG	0.34-0.50 mm²	Gold 15µ"
MP20W23G30	MS20W23G30	22-20AWG	0.34-0.50 mm²	Gold 30µ"
MP24W23F	MS24W23F	26-24AWG	0.14-0.25 mm²	Gold Flash
MP24W23G5	MS24W23G5	26-24AWG	0.14-0.25 mm²	Gold 5µ"
MP24W23G10	MS24W23G10	26-24AWG	0.14-0.25 mm²	Gold 10µ"
MP24W23G15	MS24W23G15	26-24AWG	0.14-0.25 mm²	Gold 15µ"
MP24W23G30	MS24W23G30	26-24AWG	0.14-0.25 mm²	Gold 30µ"
MP28W23F	MS28W23F	30-28AWG	0.05-0.08 mm²	Gold Flash
MP28W23G5	MS28W23G5	30-28AWG	0.05-0.08 mm²	Gold 5µ"
MP28W23G10	MS28W23G10	30-28AWG	0.05-0.08 mm²	Gold 10µ"
MP28W23G15	MS28W23G15	30-28AWG	0.05-0.08 mm²	Gold 15µ"
MP28W23G30	MS28W23G30	30-28AWG	0.05-0.08 mm²	Gold 30µ"

Machined, Tooling	
Part Number	Description
AUTK-20	Hand Crimp Tool, Size 20
AUTK-100	Universal Heavy Duty Contact Crimping Tool Kit, Size 12/16/20
MFX-3959	Hand Crimp Tool for Machined Contacts
MFX-3960	Pneumatic Crimp Tool for Machined Contact

Plating Options, All	
Symbol	Plating
T	Tin Plated (for Stamped & Formed Contacts)
S	Silver Plated 5Um (for Machined Contacts)
F	Gold Plated
G5	Gold Plated (Thickness 5µ")
G10	Gold Plated (Thickness 10µ")
G15	Gold Plated (Thickness 15µ")
G30	Gold Plated (Thickness 30µ")

Stamped & Formed , Crimp Contacts				
Part Number		Contact Size (AWG)	Wire Range (mm²)	Plating
Male	Female			
SP20W2F	SS20W2F	22-20AWG	0.34-0.50 mm²	Gold Flash
SP20W2G5	SS20W2G5	22-20AWG	0.34-0.50 mm²	Gold 5µ"
SP20W2G10	SS20W2G10	22-20AWG	0.34-0.50 mm²	Gold 10µ"
SP20W2G15	SS20W2G15	22-20AWG	0.34-0.50 mm²	Gold 15µ"
SP20W2G30	SS20W2G30	22-20AWG	0.34-0.50 mm²	Gold 30µ"
SP24W2F	SS24W2F	26-24AWG	0.14-0.25 mm²	Gold Flash
SP24W2G5	SS24W2G5	26-24AWG	0.14-0.25 mm²	Gold 5µ"
SP24W2G10	SS24W2G10	26-24AWG	0.14-0.25 mm²	Gold 10µ"
SP24W2G15	SS24W2G15	26-24AWG	0.14-0.25 mm²	Gold 15µ"
SP24W2G30	SS24W2G30	26-24AWG	0.14-0.25 mm²	Gold 30µ"
SP28W2F	SS28W2F	30-28AWG	0.05-0.08 mm²	Gold Flash
SP28W2G5	SS28W2G5	30-28AWG	0.05-0.08 mm²	Gold 5µ"
SP28W2G10	SS28W2G10	30-28AWG	0.05-0.08 mm²	Gold 10µ"
SP28W2G15	SS28W2G15	30-28AWG	0.05-0.08 mm²	Gold 15µ"
SP28W2G30	SS28W2G30	30-28AWG	0.05-0.08 mm²	Gold 30µ"

Stamped & Formed, Tooling	
Part Number	Description
MFX-3958	Hand Tool, Stamped & Formed Contact, Size 20, 20-28AWG
MFX-3957	Crimp Die for Stamped & Formed Contact

Misc Tooling, All	
Part Number	Description
AT13-204-2005	Sealing Plug, Size 20
QXRT20-ATS26P	Contact Extraction Tool, Size 20 (Used with ATS04 and ATS06)
ISRT20	Contact Insertion Tool, Size 20
FT-ATS26P	Installation Fixture for ATS04-26P (Required)
ATRT-100	Contact and Wedgelock Extraction Tool

Standard Quantity Order Options	
Machined	Bulk Package, 500 Pieces
Stamped & Formed	Reel, 3000 Pieces