


| 6    |            | 5                                  |  | 4   |     |
|------|------------|------------------------------------|--|-----|-----|
| ITEM | PART#      | DESCRIPTION                        |  | QTY | UOM |
| A,B  | 347910020  | MINI50 CONN RCPT 2CKT BR BLK POL A |  | 2   | PC  |
| C    | 5600230421 | CTX50 RCPT TERM SN M-GRIP D WIND   |  | 4   | PC  |
| D    | --         | WHITE PART ID LABEL                |  | 1   | PC  |

| 2    |    | 1                                |        |
|------|----|----------------------------------|--------|
| FROM | TO | DESCRIPTION                      | COLOUR |
| A1   | B1 | 1X0.22 SQMM DISC PVC BK FLRYW125 | BLACK  |
| A2   | B2 | 1X0.22 SQMM DISC PVC BK FLRYW125 | BLACK  |



| PART NUMBER | TITLE                         | L1    | L2(REF) |
|-------------|-------------------------------|-------|---------|
| 2240501022  | Mini50 R-R 2ckt 150mm disc Sn | 150±5 | 15      |
| 2240501023  | Mini50 R-R 2ckt 300mm disc Sn | 300±5 | 15      |
| 2240501024  | Mini50 R-R 2ckt 600mm disc Sn | 600±5 | 15      |

MOLEX P/N  
MOLEX  
BATCH WK/YR

DETAIL A

NOTES

1. CABLE ASSEMBLY TO BE TESTED 100% FOR CONTINUITY AND POLARITY.  
2. CONNECTOR VIEW SHOWN IS FROM MATING SIDE.  
3.LABEL TEXT MUST BE 2 MM MAX. IN HEIGHT WITH ARIAL FONT.  
4.LABEL MUST BE WRAPPED IN FLAG TYPE ON A SINGLE CABLE.

| REVISION        |     |                 |                     |
|-----------------|-----|-----------------|---------------------|
| DATE            | REV | DESCRIPTION     | CHANGER             |
| 03/30/2023      | A   | INITIAL RELEASE | THANUB              |
| DOCUMENT STATUS | P1  | RELEASE DATE    | 2023/04/05 04:51:04 |

| FUNCTIONAL SYMBOLS | THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION |                 |
|--------------------|-----------------------------------------------------------------------------------------------------------------------------------------------|-----------------|
|                    | DIMENSION UNITS                                                                                                                               | SCALE           |
| $\frac{F}{A} = 0$  | mm                                                                                                                                            | NTS             |
| $\frac{F}{E} = 0$  | GENERAL TOLERANCES (UNLESS SPECIFIED)                                                                                                         |                 |
| $\frac{F}{P} = 0$  | ANGULAR TOL ± °                                                                                                                               |                 |
| DIVISIONAL SYMBOLS | 4 PLACES                                                                                                                                      | ±               |
|                    | 3 PLACES                                                                                                                                      | ±               |
|                    | 2 PLACES                                                                                                                                      | ±               |
|                    | 1 PLACE                                                                                                                                       | ±               |
|                    | 0 PLACES                                                                                                                                      | ±               |
|                    | DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS                                                                                          |                 |
|                    | THIRD ANGLE PROJECTION                                                                                                                        | DRAWING         |
|                    | SERIES                                                                                                                                        | MATERIAL NUMBER |
|                    | CUSTOMER                                                                                                                                      | SHEET NUMBER    |

EC NO: 744926  
DRWN: THANUB  
CHK'D: SKUMAR07  
APPR: SKUMAR07

2023/03/30  
2023/04/05  
2023/04/05

INITIAL REVISION:  
DRWN: THANUB  
APPR: SKUMAR07

2023/03/30  
2023/04/05

DOCUMENT NUMBER  
2240501022

DOC TYPE  
PSD

DOC PART  
000

REVISION  
A

SEE TABLE

PRODUCT CUSTOMER DRAWING

SEE TABLE

GENERAL MARKET

1 OF 1