


6		5			4		3		2		1	
ITEM	PART#	DESCRIPTION			QTY	UOM			FROM	TO	DESCRIPTION	COLOUR
A	347910020	MINI50 CONN RCPT 2CKT BR BLK POL A			1	PC			A1	--	1X0.22 SQMM DISC PVC BK FLRYW125	BLACK
B	5600230421	CTX50 RCPT TERM SN M-GRIP D WIND			2	PC			A2	--	1X0.22 SQMM DISC PVC BK FLRYW125	BLACK
C	--	WHITE PART ID LABEL			1	PC						



PART NUMBER	TITLE	L1	L2(REF)
2240511022	Mini50 R-S 2ckt 150mm disc Sn	150±5	15
2240511023	Mini50 R-S 2ckt 300mm disc Sn	300±5	15
2240511024	Mini50 R-S 2ckt 600mm disc Sn	600±5	15

MOLEX P/N
MOLEX
BATCH WK/YR

DETAIL A

- NOTES
- 1.THE PRODUCT MUST MEET PERFORMANCE SPECIFICATION AS PER ES-36586-004.
 2. CONNECTOR VIEW SHOWN IS FROM MATING SIDE.
 - 3.LABEL TEXT MUST BE 2 MM MAX. IN HEIGHT WITH ARIAL FONT.
 - 4.LABEL MUST BE WRAPPED IN FLAG TYPE ON A SINGLE CABLE.
 - 5.TINNING SHOULD BE DONE WITH LEAD FREE SOLDER BAR ONLY.
 - 6.FREE ENDS MUST BE STRIPPED,TWISTED & TINNED.
 - 7.THE LENGTH OF TINNING IS 5±1 MM.TINNING DIA MUST BE 0.90 MM MAX.

REVISION				
DATE	REV	DESCRIPTION	CHANGER	
03/30/2023	A	INITIAL RELEASE	THANUB	
RELEASE STATUS	P1	RELEASE DATE	2023/04/05	04:51:05

FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																	
	DIMENSION UNITS		SCALE		CURRENT REV DESC:				molex									
	mm		NTS															
	GENERAL TOLERANCES (UNLESS SPECIFIED)								EC NO: 744926 DRWN: THANUB2023/03/30 CHK'D: SKUMAR072023/04/05 APPR: SKUMAR072023/04/05 INITIAL REVISION: DRWN: THANUB2023/03/30 APPR: SKUMAR072023/04/05									
ANGULAR TOL ± °																		
4 PLACES		±																
3 PLACES		±																
2 PLACES		±																
DIVISIONAL SYMBOLS	1 PLACE		±		PRODUCT CUSTOMER DRAWING													
	0 PLACES		±															
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		DOCUMENT NUMBER		DOC TYPE		DOC PART		REVISION	
							A4-SIZE		224051		2240511022		PSD		000		A	
										SEE TABLE		GENERAL MARKET		1 OF 1				