




NOTES:
CABLE:
CABLE TYPE 12:
AWG 22 $\varnothing 6.8 \pm 0.2 \text{ mm}$ UL STYLE 21215
MIN. BENDING RADIUS: 7.5xD
COLOR: GREEN RAL 6018, MATERIAL: PUR
TEMPRETURE RATING (FIXED): -40 °C TO +80 °C
TEMPRETURE RATING (FLEXIBLE): -10 °C TO +70 °C

CABLE TYPE 16:
AWG 26/24 $\varnothing 6.5 \pm 0.2 \text{ mm}$ UL STYLE 21215
MIN. BENDING RADIUS: 7.5xD
COLOR: TEAL, MATERIAL: TPU
TEMPRETURE RATING (FIXED): -40 °C TO +80 °C
TEMPRETURE RATING (FLEXIBLE): -10 °C TO +70 °C


ELECTRICAL DATA:
POLES: 4, D-CODING
VOLTAGE RATING: 250V (UL)
CURRENT RATING: 4 A
INSULATION RESISTANCE. $10^8 \Omega$ MIN.
TRANSMISSION CHARACTERISTICS ACCORDING TO ISO/IEC 11801 CATEGORY 5e
PATCH CORD PROFINET TYPE C

ENVIRONMENTAL:
PROTECTION: IP67 For both, cable 16 and cable 12 in mated and locked position.
IP69k only with Cable 12 in mated and locked position.
MATING CYCLES: MIN. 100
TEMPERATURE RATING PLUG: -40°C TO +85°C


BOM				
ITEM	QTY.	DESCRIPTION	MATERIAL	FINISH/COLOR
1	-	OVERMOLD	TPC	BLACK
2	-	CABLE	SEE NOTES	SEE NOTES
3	1	SLEEVE SHLD STR	BRASS	NICKEL
4	1	M12-CLOSURE CAP-90 SHIELDED	BRASS	Ni-PLATED
5	8	CONTACT MALE	BRASS	SELECTIVE GOLD
6	2	PLUG U12 4P DC MA SHLD	-	-

DOCUMENT STATUS	P1	RELEASE DATE	2023/11/21	12:10:37
-----------------	----	--------------	------------	----------

FORMAT: master-tb
REVISION: J1
DATE: 2021/05/01



CABLE PRINTING :
Molex PN OLD ENG NO MX(YYWW*)
*Where - YY-Year, WW-Week
Example for production date year 2022 week 42:
Molex 1204061025 EYYAS6212M010 MX2242



SCALE 1:2

PART LIST			
MOLEX NO.	ENGINEERING NO.	LENGTH (mm)	RAW CABLE
1204061025	EYYAS6212M010	1000	CABLE 12
1204061026	EYYAS6212M020	2000	CABLE 12
1204061027	EYYAS6212M050	5000	CABLE 12
1204061028	EYYAS6212M100	10000	CABLE 12
1204061029	EYYAS6216M010	1000	CABLE 16
1204061030	EYYAS6216M020	2000	CABLE 16
1204061031	EYYAS6216M050	5000	CABLE 16
1204061032	EYYAS6216M100	10000	CABLE 16

FUNCTIONAL SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		DRAWING NO.		SHEET NO.	
FA = 0 FE = 0 FF = 0		DIMENSION UNITS mm		SCALE 2:1		CURRENT REV DESC: CHANGED FROM MOLEX INTERNAL TO GENERAL MARKET	
		GENERAL TOLERANCES (UNLESS SPECIFIED)				molex	
		ANGULAR TOL ± 1.0 °		EC NO: 769484		CSE U12 4P DC MA STR WSOR RA XM DE SHLD	
		4 PLACES ±		DRWN: RSCHIEBER 2023/11/21			
DIVISIONAL SYMBOLS		3 PLACES ±		CHK'D: RSILLER 2023/11/21			
		2 PLACES ± 0.05		APPR: RSILLER 2023/11/21		PRODUCT CUSTOMER DRAWING	
		1 PLACE ± 0.3		INITIAL REVISION:		DOCUMENT NUMBER	
		0 PLACES ± 0.5		DRWN: ARPITT 2022/08/10		1204061025	
				APPR: RSILLER 2023/07/14		DOC TYPE	
						DOC PART	
						REVISION	
						A1	
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		DRAWING	
		SHEET NUMBER		SERIES		MATERIAL NUMBER	
		1 OF 2		A3-SIZE		120406	
		SEE PART LIST		CUSTOMER		GENERAL MARKET	

LENGTH	TOLERANCE
0 m-1 m	+40 mm
>1 m-5 m	+60 mm
>5 m-10 m	+80 mm
>10 m-20 m	+140 mm
>20 m-30 m	+160 mm
>30 m	+1% length

