







MATERIALS AND FINISHES:

BODY: STAINLESS STEEL
PLATED: PASSIVATE


CENTER CONTACT: BERYLLIUM COPPER
PLATED: GOLD (50μ-in) MIN
OVER NICKEL (100μ -in) MIN

INSULATOR: PTFE

SCREW: STAINLESS STEEL
PLATED: PASSIVATE



SEE SHEET 2 FOR PART NUMBERS	
PS-89675-3460	ELECTO/MECH PERFOR
MIL-STD-348B, FIG 310-2	INTERFACE
SPECIFICATION	DESCRIPTION

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
DIMENSION UNITS		SCALE		CURRENT REV DESC: SEE ECM 117632	molex				
INCH									
GENERAL TOLERANCES (UNLESS SPECIFIED)					EC NO: 174360 DRWN: PSWAMI02 2018/04/04 CHK'D: PSWAMI02 2018/04/04 APPR: AROBERTSON 2018/04/04				
	MM	INCH							
4 PLACES	±	±							
3 PLACES	±	±							
2 PLACES	±	±							
1 PLACE	±	±							
0 PLACES	±	±							
ANGULAR TOL		±	°	INITIAL REVISION:		PRODUCT CUSTOMER DRAWING			
				DRWN: PSWAMI02 2017/06/01 APPR: AROBERTSON 2017/06/01					
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION	DRAWING	SERIES	MATERIAL NUMBER	CUSTOMER	SHEET NUMBER
					C-SIZE	73251	SEE TABLE		1 OF 3



DOCUMENT STATUS	P1	RELEASE DATE	2018/04/04	13:36:29
-----------------	----	--------------	------------	----------

MATERIALS AND FINISHES


SEE SHEET 1


PCB LAYOUT

SEE SHEET 1







C	73251-1856	4.76 / .188	.062+.040/-0.01	1.57+1.02/-0.25	2	SINGLE BAG	IN BAG
	73251-1855	3.18/ .125	.050+.00/-0.040	1.27+0.00/-1.02	2	TRAY	BULK
	73251-1854	9.53/ .375	.255+.040/-0.02	6.48+1.02/-0.51	2	TRAY	BULK
	73251-1853	6.35/ .250	.130+.040/-0.02	3.30+1.02/-0.51	2	TRAY	BULK
	73251-1852	N/A	N/A	N/A	NO SCREW	SINGLE BAG	NONE
B	73251-1851	4.76/ .188	.062+.040/-0.01	1.57+1.02/-0.25	2	TRAY	BULK
	73251-1850	N/A	N/A	N/A	NO SCREW	TRAY	NONE
	PART NO.	(MM/IN)	IN	MM	SCREWS (QTY)	PACKAGING	SCREW PACKAGING
		DIM A	DIM B				

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION													
DIMENSION UNITS		SCALE		CURRENT REV DESC: SEE ECM 117632				molex					
INCH													
GENERAL TOLERANCES (UNLESS SPECIFIED)				SMA JACK, 2H FLG WITH 0-80 THD, 50 OHM 27 GHZ SMA-JR/F, EWR-10959-A									
	MM	INCH											
4 PLACES	±	±											
3 PLACES	±	±											
2 PLACES	±	±											
1 PLACE	±	±		PRODUCT CUSTOMER DRAWING									
0 PLACES	±	±											
ANGULAR TOL				±		°		DOCUMENT NUMBER		DOC TYPE	DOC PART	REVISION	
								SD-73251-185		PSD	000	B21	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER	SHEET NUMBER
						C-SIZE		73251		SEE TABLE			2 OF 3




SCREW: STAINLESS STEEL
PLATED: PASSIVATE



PS-89675-3460	ELECTO/MECH PERFOR
MIL-STD-348B, FIG 310-2	SMA JACK INTERFACE
SPECIFICATION	DESCRIPTION

					THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION												
					DIMENSION UNITS		SCALE		CURRENT REV DESC: SEE ECR				molex				
					INCH		NTS										
					GENERAL TOLERANCES (UNLESS SPECIFIED)												
						MM	INCH										
					4 PLACES	±		±	EC NO: 613729 DRWN: LMEIER 2019/03/12 CHK'D: SSSHAH 2019/03/15 APPR: AROBERTSON 2019/03/15				SMA JACK, FLANGE WITH 0-80 THD, 50 OHM 27 GHZ SMA-J/R/F, EWR-10959				
					3 PLACES	±		± 0.01									
					2 PLACES	± 0.25	±										
					1 PLACE	±	±										
					0 PLACES	±		±	INITIAL REVISION: DRWN: APRAKASH01 2016/10/21 APPR: AROBERTSON 2017/02/21				DOCUMENT NUMBER		DOC TYPE	DOC PART	REVISION
					ANGULAR TOL ± 2.0 °								SD-73251-348		PSD	000	A13
					DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING	SERIES	MATERIAL NUMBER		CUSTOMER		SHEET NUMBER
											C-SIZE	73251	SEE TABLE				1 OF 2
DOCUMENT STATUS	P1	RELEASE DATE	2019/03/15	15:32:57													

PCB LAYOUT: SEE SHEET 1



73251-3485	.125/3.18	.050+.00/-0.040	1.27+0.00/-1.02	2	TRAY	BULK
73251-3484	.375/9.52	.255+.040/-0.02	6.48+1.02/-0.51	2	TRAY	BULK
73251-3483	.250/6.35	.130+.040/-0.02	3.30+1.02/-0.51	2	TRAY	BULK
73251-3482	N/A	N/A	N/A	NO SCREW	SINGLE BAG	NONE
73251-3481	.188/4.76	.062+.040/-0.01	1.57+1.02/-0.25	2	TRAY	BULK
73251-3480	N/A	N/A	N/A	NO SCREW	TRAY	NONE
PART NO.	(IN/MM)	IN	MM	SCREWS (QTY)	PACKAGING	SCREW PACKAGING
	DIM A	DIM B				

DOCUMENT STATUS	P1	RELEASE DATE	2019/03/15	15:32:57
12		11	10	