


LOCATE HOLES
 $\Phi 0.13 \begin{bmatrix} .005 \end{bmatrix}$
 POSITION DIMENSIONS
 ARE BASIC



MATERIALS:

RJ:

HOUSING & COVER: ENGINEERING THERMOPLASTIC
 FLAMMABILITY RATING UL 94V-0, COLOUR: BLACK

CONTACTS: PHOSPHOR BRONZE

PLATING: SELECTIVE GOLD PLATING ON MATING SURFACES
 SEE AMPHENOL PART NUMBER FOR DETAIL.

50 μ " [1.27 MICRONS]

MIN. NICKEL UNDERPLATE

GOLD FLASH ON CONTACT TAILS.

SHIELD: BRASS PLATED WITH NICKEL.

USB:

HOUSING: ENGINEERING THERMOPLASTIC
 FLAMMABILITY RATING UL 94V-0,
 COLOUR: BLACK

CONTACTS: PHOSPHOR BRONZE

PLATING: SELECTIVE GOLD FLASH ON MATING SURFACES

50 μ " [1.27 MICRONS]

MIN. NICKEL UNDERPLATE

100 μ " TIN PLATING ON CONTACT TAILS

SHIELD: BRASS PLATED WITH NICKEL.

AMPHENOL PARTNUMBER: RJE36-188-3X01

GOLD PLATING

0 = GOLD FLASH

1 = 6 μ INCH

2 = 15 μ INCH

3 = 30 μ INCH

4 = 50 μ INCH

UNLESS SPECIFIED OTHERWISE	DRAWN <i>HANSON.C</i>	DATE <i>FEB 27/19</i>
PRIMARY UNITS MILLIMETER	CHECKED	
SECONDARY	M.E. APP'D	
REFERENCE IN PARENTHESES	Q.A. APP'D	
GENERAL TOLERANCES	DWG APPR. <i>L.CHAN</i>	<i>FEB 27/19</i>
1 DECIMAL PLACE ±0.30	ENG. REL. NO.	
2 DECIMAL PLACES ±0.25	REF.	
3 DECIMAL PLACES ±0.20	THIRD ANGLE PROJECTION	DO NOT SCALE DRAWING
ANGULAR DEGREES ±1.0°		

Amphenol Canada Corp.	
Commercial Products	
TITLE	
RJ45 OVER TWO USB 2.0 COMBO, DIP TYPE	
WITH TABS -RoHS COMPLIANT	
DWG. NO.	REV
P-RJE36-188-3X01	A
CODE ID NO. 03554	DWG SIZE: C
SCALE: N/A	SHEET 1 OF 1