




- NOTE:
1. MATERIAL- C1010 BRIGHT BASIC WIRE
 2. FINISH BRIGHT NICKEL- CHROME 0.01mm MIN
 3. RIBS ARE $\text{Ø}1.6\text{mm}$
 4. WELD JOINTS TO WITHSTAND 100 LBS PULL FORCE
 5. SURFACE TO BE FLAT WITHIN 1.52mm
 6. GENERAL TOLERANCE UNLESS NOTED ± 0.5
 7. UNIT: mm
 8. PART MEETS $\text{Ø}6.35\text{mm}$ PLUG GAUGE TEST

WHEN UNSPECIFIED,
 frac = $\pm \frac{1}{32}$
 .X = $\pm \frac{1}{16} - .015$
 .XX = $\pm \frac{1}{16} - .010$
 .XXX = $\pm \frac{1}{16} - .005$
 angle = $\pm \frac{1}{2} - .5$ deg.

REV.	DATE	MATERIAL	DATE
A	2-8-89		
DESIGNED BY	S.P.	PART NUMBER	
SUNON Inc.		FG-4	