


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER	QTY. - BATTERY	QTY. - CHARGER	TOTAL WEIGHT LBS [kg]
PBTMT	2 - 12 VOLT LITHIUM-ION	1 - 115 VOLT, 60 Hz	3.7 [1.8]
PBTMT/E	2 - 12 VOLT LITHIUM-ION	1 - 220 VOLT, 50 Hz	



GENERAL NOTES:

1. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
2. DIMENSIONS IN [BRACKETS] ARE IN MILLIMETERS. ALL DIMENSIONS ARE FOR REFERENCE ONLY.
3. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS (EUROPEAN DIRECTIVE 2011/65/EU ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.

TOOL SPECIFIC / TECHNICAL INFORMATION:

1. THE PBTMT AND PBTMT/E ARE BATTERY POWERED INSTALLATION TOOLS.
2. THE INSTALLATION TOOLS ARE USED FOR STAINLESS STEEL CABLE TIES AND BANDING. GO TO www.panduit.com FOR MORE INFORMATION.
3. A COPY OF OPERATION MANUAL AND SYSTEM SPECIFICATIONS CAN BE FOUND AT: www.panduit.com.
4. THE TOOLS HAVE BUILT IN AUTOMATIC FLUSH CUT OFF AND CONTROLLED TENSION MECHANISM.

PART NUMBER		SEE TABLE		
TITLE		PBTMT, PBTMT/E TOOL		
		CUSTOMER DRAWING		
ITEM REVISION NAME		03259NEC/00		
DATASET FILE NAME		03259NEC_DC/00A		
		THIRD ANGLE PROJECTION		
MATERIAL		SEE NOTES		
		DRAWING NUMBER 03259NEC-DC		
DRAWN BY	DATE	CHK	SCALE	SIZE
JBN	05-18-23	MRJS JOCI	NONE	A
SHEET 1 OF 1				

A-SIZE CUSTOMER

00A	05-18-23	JBN	MRJS JOCI	HAH	INITIAL RELEASE	130799/00
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN