



DIMENSIONS:	
L	1.625" ± 0.030
W	1.313" ± 0.030
H	1.313" ± 0.030
A	0.250" ± 0.030
B	0.350" ± 0.030
C	1.280" ± 0.030
D	0.041" x 0.018" ± 0.005
G	0.125" ± 0.005
M	1.063" ± 0.030



ELECTRICAL DATA:			
TESTS	CONDITIONS	ACCEPTANCE CRITERIA	
lex	@ 115V, 60Hz, PIN 1 - PIN 2	46.8mA	Max.
Sec. N.L.V	@ 115V, 60Hz, PIN 1 - PIN 2		
	PIN 3 - PIN 4 =	115.0V	$\pm 2\%$
	PIN 5 - PIN 6 =	34.12V	$\pm 2\%$
	PIN 7 - PIN 8 =	34.12V	$\pm 2\%$
DCR	@ 20°C, PIN 1 - PIN 2 =	257.9 Ω	$\pm 20\%$
	@ 20°C, PIN 3 - PIN 4 =	257.9 Ω	$\pm 20\%$
	@ 20°C, PIN 5 - PIN 6 =	19.65 Ω	$\pm 20\%$
	@ 20°C, PIN 7 - PIN 8 =	19.65 Ω	$\pm 20\%$
HIPOT	PRIMARY - SECONDARY	2500V, 60Hz, 1 SEC	

REV.#	REVISION	DATE	HAMMOND ELECTRONIC DIVISION			
0	RELEASED.	C.I. 12/18/17	52 RANKIN PLACE, WATERLOO, ONTARIO, N2J 3Z5			
			DWG. BY: C. ILIE	CHK'D BY:	TITLE: PC BOARD MOUNT	DWG. NO.
			DATE: 12/18/17	APP'D. BY:	POWER TRANSFORMER	162F56
				DIMENSIONS: IN(X) MM()		

PH # (519) 886-6181
FAX # (519) 886-9540