




316 STAINLESS STEEL
HINGE PIN


(2) EACH #10-32 BRASS
INSERTS, AND 316 STAINLESS
STEEL CAPTIVE COVER TAMPER
PROOF SCREWS WITH
RETAINING O-RINGS

FIP
POLYURETHANE
GASKET

.14 [3.7]



SECTION B-B

FIP
POLYURETHANE
GASKET



SECTION A-A

TOP VIEW WITH
COVER OFF




MOUNTING HOLE
PATTERN HMI108

NOTE:

1. DATA SUBJECT TO CHANGE
2. WILL FIT ENCLOSURE
SIZES 12X10 AND LARGER

MATERIAL:
BOX- INJECTION POLYCARBONATE
STANDARD COVER- INJECTION POLYCARBONATE
CLEAR COVER- INJECTION POLYCARBONATE



PART No. PJHMI108HTP

for more information visit
www.hammfg.com
Data subject to change without notice
Drawing Not to Scale