


www.hammondmfg.com

266LA25

Power Transformer - Low Voltage/Filament
Dual Primary & Secondary - Open Style Chassis Mount



| Overall Dimensions (in / mm) | |
|-------------------------------|------------------------|
| A | 3.69 / 94 |
| В | 2.13 / 54 |
| C D | 2.31 / 59 |
| D | 3.13 / 80 |
| Е | 3.13 / - |
| Weight | 2.69 lbs / 1.22 kg |
| Mounting Hole Sizes (in / mm) | |
| Width-wise | 0.187 /5 |
| Depth-wise | / |
| Electrical | |
| Size (VA) | 50.4 |
| Primary | 117/234 VAC, 50/60 Hz. |
| Secondary Series (C.T.) | 25.2V C.T. @ 2A |
| Secondary Parallel | - |

Features

- Primary 117/234 VAC, 50/60 Hz.
- All units have dual secondaries except 266LA25 (C.T. secondary only). If you only require a single primary & secondary check out our more economical 166 Series.
- Secondaries can be used as; a center tapped secondary, parallel connected or used individually (except 266LA25).
- Units are designed for use with all windings engaged.
- · Open style.
- Minimum 6" long leads.
- Dual bobbin design no electrostatic shield required.
- We use Class B insulation (130 degrees, C) for extra protection UL listed as a Class A (105 degree, C) design
- Hi-Pot test of 2,000V RMS.
- UL listed (# E207860) Type 3AH
- CSA certified (209651)

Connection Information 266 Series Power Transformers

