




## D.C. Reactors or Filter Chokes Low to Medium Current

### Features

- Economical “open bracket” - channel mount.
- Tolerance of 15% on both inductance & resistance.
- Inductances measured at rated D.C. current.
- Minimum 5” long leads.
- Units will exhibit less inductance at slightly higher currents or more inductance at lower currents.
- Perfect for high voltage power supply filtering.
- Every unit is Hipot tested (100%) at 1,500 VAC
- Units are vacuum impregnated with polyurethane varnish for quiet and long life operation.



Mechanical	
A	3.69" / 93.7 mm
B	2" / 50.8 mm
C	2.31" / 58.7 mm
D	3.13" / 79.5 mm
G	0.19" / 4.8 mm
Weight	1.7 lbs / 0.77 kg
Electrical	
Inductance (+/- 15%)	1.5H
D.C. Current	300 ma.
Resistance (+/- 15%)	40 ohms
Maximum Operating Volt (D.C.)	400V