





TOLERANCE UNLESS OTHERWISE SPECIFIED	
.XX	±0.15

THIS IS A C.A.D. GENERATED DRAWING
DO NOT MAKE MANUAL REVISIONS TO MASTER.



ISSUE NUMBER	
ORIGINAL	①
ADD NOTE 5 & 6	
P.M.	AUG. 13/2023 ②
REVISE NOTE 2 & DELETE DIM DELETE DIM R1.70, Ø1.10, R1.20	
L.K.	AUG. 18/2023 ③
ADD, PIN 1 LOCATION	
P.M.	SEP. 26/2023 ④



SPECIFICATION:

1- MATERIAL:

CONTACT: BRASS, GOLD FLASH PLATING ALL OVER NICKEL UNDERPLATING
HOUSING: PA46, BLACK
MAGNET: N52

2- ELECTRICAL:

RATED VOLTAGE (PER CONTACT): 12V
RATED CURRENT (PER CONTACT): 2A

3- MECHANICAL LIFE: 10,000 CYCLES MIN.

4- WORKING TEMPERATURE RANGE: -30~+85°C

5- RECOMMENDED SOLDERING PROCESS ARE SELECTIVE SOLDERING OR MANUAL SOLDERING. OTHER FORMS OF SOLDERING SUCH AS WAVE SOLDER OR REFLOW SOLDER ARE NOT RECOMMENDED AND CAN POTENTIALLY CAUSE DEMAGNETIZATION OF MAGNET IN THE CONNECTOR

6- MATING WITH: 687L0421A501200 OR 685L0421250110E



THIS SERIES FULLY CONFORMS TO
THE EUROPEAN UNION DIRECTIVES
2011/65/EU FOR RoHS COMPLIANCY.



YOUR CONNECTION TO QUALITY & SERVICE

EDAC INC
TORONTO, ONTARIO
CANADA

THESE DRAWINGS AND SPECIFICATIONS
ARE THE PROPERTY OF EDAC INC., AND
SHALL NOT BE REPRODUCED, OR COPIED
OR USED AS THE BASIS FOR THE
MANUFACTURE OR SALE OF APPARATUS
WITHOUT WRITTEN PERMISSION.

MAGNETIC SPRING LOADED CONNECTOR, 4POS, FEMALE	ACAD REFERENCE NO.: 686L0421350120E	UNIT: MM
	DRAWN: J.L.	DATE: 2023-09-27
	CHECKED: R.S.M	DATE: 2023-09-27
	SCALE: (IN CAD 1:1)	SHEET 1 OF 1
	DRAWING NUMBER: 686L0421350120E	ISSUE 4
PART NUMBER: 686L0421350120E		