




PART NUMBER	MADE FROM	CONTACT SIZE	WIRE SIZE	A DIA REF	B DIA REF	C REF	E DIA REF	MEAN SURFACE AREA SQ IN.	WT-LB
10-407979-1	10-407979-1B	12	20,18,16	.065	.094	.167	.138	.1179	
-2	-2B	12	24,22,20	.046	.094	.	.138	.1102	
-10	-10B	16	22,24,26,28	.043	.059		.091	.1137	
-20	-20B	20	26,28	.026	.040		.065	.0434	

54508-52		REVISIONS		
ZONE	LTR	DESCRIPTION	DATE	APPROVED
A	1			
A2		WAS 10-407919-1B (MADE FROM, COL.) ECN: CNR	UHLIG 8-26-70	<i>[Signature]</i>
A3		STANDARDIZED NOTE 1. ADDED COL E & DATA, -XF & DATA ECN: CNR	A. HANNI 2-16-71	<i>[Signature]</i>
B		(MFG) ADDED -X5 96800-5 TO NOTE 1. ECN: 59641-1	4-24-78 D. Wilkinson	<i>[Signature]</i>
C		(CL II) ADDED '22' TO WIRE SIZE FOR P/N 10-407979-10() AND CHG'D BX TO AAO ECN: B4253	8-7-12 JONES	



CONTACT SIZE 20

2. FOR RELEASE STATUS OF DESIRED PART SEE APPLICABLE PARTS LIST.
1. TO COMPLETE PART NUMBER, ADD APPLICABLE LAST DIGIT TO SUFFIX FOR DESIRED FINISH.

SUFFIX	FINISH
-X2	GOLD PLATE 9-6800-2
-X3	9-6800-3
-X4	9-6800-4
-XF	9-6800-F
-X5	9-6800-5

NOTES:

FIND NO.	QTY REQD	CODE IDENT	PART NUMBER	DESCRIPTION	NOTE REF
PARTS LIST					
UNLESS OTHERWISE SPECIFIED LINEAR DIMENSIONS ARE IN INCHES. TOLERANCES: .XXX ± .010, .XX ± .03, .X ± .1, ANGLES ± 2°. OTHER STANDARDS PER 9-3800 AND MIL-D-1000. NOTE REF			SIGNATURES PREPARED <i>H. UHLIG</i> CHECKED <i>S.A. Lord</i> MATERIAL <i>Bureau</i> APPROVED <i>H. Uhlrig</i> APPROVED <i>[Signature]</i>	DATES 6-2-70 2-17-71 2-17-71 7-22-70	AMPHENOL CORPORATION 40-60 DELAWARE AVENUE SIDNEY, NEW YORK TITLE: SLEEVE, WIRE ADAPTER, SOLDERLESS CONTACT, ELECTRICAL CONNECTOR, TYPE JT-R
MATERIAL SPEC			PROCESS SPEC SEE NOTE 1		
SIZE C			CODE IDENT NO. 77820		
SCALE NONE			WT SEE COLUMN		
REF 10-74696			SHEET		