







REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	10AUG2023	RZ	HL



- NOTES:
1. MATERIAL
PLASTIC PARTS: LCP, UL 94V-0
SIGNAL CONTACT: COPPER NICKEL SILICON ALLOY
GROUND SHIELD: PHOSPHOR BRONZE
CLIP: STAINLESS STEEL
2. FINISH: CONTACT AND SHIELD
MATING AREA:
MEET PERFORMANCE REQUIREMENT OF TE CONNECTIVITY
PRODUCT SPECIFICATION 108-115174.
- COMPLIANT PIN AREA.
0.5um MIN MATTE TIN OVER NICKEL UNDERPLATING.
3. PLATING THROUGH HOLE SPECIFICATION:
SIGNAL:
DRILL HOLE 0.40±0.020,
COPPER PLATING 0.0375±0.0125.
FINISH HOLE: 0.31REF
GROUND A:
DRILL HOLE 0.45±0.020,
COPPER PLATING 0.0375±0.0125.
FINISH HOLE: 0.36REF
GROUND B:
DRILL HOLE 0.40±0.020,
COPPER PLATING 0.0375±0.0125.
FINISH HOLE: 0.31REF
- MORE INFORMATION ABOUT PLATING THROUGH HOLE PLEASE REFER
TO APPLICATION SPECIFICATION.
4. PART NUMBER & DATE CODE MARKING IN APPROXIMATE AREA AS SHOWN.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RICHARD ZHOU 10AUG2023	 TE Connectivity	
		CHK MIKE CHEN 10AUG2023		
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME eZd PLUS PLUS, ASSEMBLY, RECEPTACLE RIGHT ANGLE, 3PAIR, 10COL
mm				
	0 P L C	+1		APVD HOPE LW 10AUG2023
	1 P L C	±0.3		
	2 P L C	±0.20		
	3 P L C	±0.200		
	4 P L C	±0.200		
ANGLES		+1		PRODUCT SPEC 108-115174
MATERIAL		FINISH		APPLICATION SPEC 114-160011
	WEIGHT		RESTRICTED TO	
	A -		C=2472336	
		CUSTOMER DRAWING		SCALE 5:1 SHEET 1 OF 1 REV A