







- NOTES:
- 1. VOLTAGE: 60 V AC
 - 2. CURRENT: 4 A AC
 - 3. DATA RATE: 10 Mbit/s // 100 Mbit/s // 1 Gbit/s
 - 4. STATIC TEMPERATURE: -40 °C TO 80 °C
 - 5. DYNAMIC TEMPERATURE: -25 °C TO 80 °C
 - 6. MATING CYCLES: 1000
 - 7. PROTECTION: IP20 (IN MATED CONDITION)
 - 8. DESIGNED ACC.
 - IEC63171-6
 - IEEE 802.3bu
 - IEEE 802.3cg
 - IEEE 802.3bw
 - IEEE 802.3bp
 - IEEE 802.3ch
 - IEC 60332-1-2
 - EN 60811-404

BOM				
ITEM	QTY	DESCRIPTION	MATERIAL	FINISH/COLOR
1	1	CABLE 1x2 AWG26/19	PUR	GREEN
2	1	SPE SHIELD SHELL	COPPER	NI PLATED
3	1	SPE CONTACT CARRIER	PA	BLACK
4	2	SPE CONTACT AWG22	COPPER	AU PLATED
5	2	Overmoulding	PUR	BLACK



FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION														
F = 0 F = 0 F P = 0 DIVISIONAL SYMBOLS	DIMENSION UNITS		SCALE	CURRENT REV DESC: EC NO: 726259 DRWN: MBLOESER 2022/11/02 CHK'D: THAERDT 2022/11/02 APPR: THAERDT 2022/11/02 INITIAL REVISION: DRWN: MBLOESER 2022/08/19 APPR: THAERDT 2022/11/02				molex SPE IP20 1X2XAWG26 / 19 PUR 0,2M							
	mm		1:1												
	GENERAL TOLERANCES (UNLESS SPECIFIED)														
	ANGULAR TOL		± 1.0 °												
	4 PLACES		±												
	3 PLACES		±												
	2 PLACES		± 0.05												
	1 PLACE		± 0.1												
	0 PLACES		± 0.2												
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
						B-SIZE		220957		2209570101		GENERAL MARKET		1 OF 2	

DOCUMENT STATUS	P1	RELEASE DATE	2022/11/02	13:30:34
-----------------	----	--------------	------------	----------

