





UNLESS SPECIFIED OTHERWISE		DRAWN RONNIE.C		OCT29/21		Amphenol Canada Corp. Commercial Products			
PRIMARY UNITS MILLIMETERS		CHECKED KELVIN.T		OCT29/21					
SECONDARY INCHES		M.E. APP'D				VERTICAL MODULAR JACK SINGLE PORTS, 8 POSITION, 8 CONTACTS, WITH LED, SHIELDED, CAT.5e TRAY PACKAGING -RoHS COMPLIANT			
REFERENCE IN PARENTHESES		Q.A. APP'D							
GENERAL TOLERANCES		DWG APP'D							
1 DECIMAL PLACE		ENG. REL. NO.				DWG NO. P-RJE44-188-1XX1 REV B			
2 DECIMAL PLACES ±0.38		REF. EAR# RJ21060							
3 DECIMAL PLACES		THIRD ANGLE PROJECTION		DO NOT SCALE DRAWING					
ANGULAR DEGREES						CODE ID NO. 03554 DWG SIZE X SCALE N/A SHEET 1 OF 3			



TYPICAL FOR SINGLE & MULTI-PORT



LED SCHEMATIC



LED SCHEMATIC

EXAMPLE:

AMPHENOL PART NUMBER: RJE44-188-1XX1

LED COLOR CODE

CODE	LED 2 (LEFT)	LED 1 (RIGHT)	CODE	LED 2 (LEFT)	LED 1 (RIGHT)	CODE	LED 2 (LEFT)	LED 1 (RIGHT)
0	BLOCKED	BLOCKED	9	GREEN	BLOCKED	J	BiC RD/GR	YELLOW
1	YELLOW	GREEN	A	BiC GR/YE	BiC GR/YE	K	YELLOW	BiC GR/OR
2	BLOCKED	GREEN	B	BiC RD/GR	BiC RD/GR	L	BiC GR/YE	RED
3	YELLOW	BLOCKED	C	BiC RD/GR	BiC GR/YE	M	RED	YELLOW
4	GREEN	YELLOW	D	GREEN	BiC GR/YE	N	BiC GR/RD	BiC GR/YE
5	GREEN	GREEN	E	YELLOW	BiC GR/YE	P	GREEN	BiC RD/GR
6	YELLOW	YELLOW	F	BiC GR/YE	YELLOW	R	BiC GR/OR	GREEN
7	RED	GREEN	G	BiC GR/OR	BiC GR/OR	T	RED	RED
8	GREEN	RED	H	BiC GR/YE	GREEN	V	BiC RD/GR	GREEN

LED SPECIFICATIONS:

FORWARD VOLTAGE: 2.1 VOLTS TYP.

REVERSE VOLTAGE: 5.0 VOLTS MIN.

LUMINOUS INTENSITY: 6~60 mCd MIN.
(AT If=20mA)

STORAGE TEMPERATURE: -40° TO 85° C

PLATING ON TAILS: TIN OR TIN/COPPER
ALLOY OVER SILVER

PRIMARY COLOR FOR BI-COLOR

LEDs IN STANDARD ANODE/
CATHODE CONFIGURATION IS:

RED-GREEN= RED

RED-YELLOW= RED

GREEN-YELLOW= GREEN

GREEN-ORANGE= GREEN

LEGEND

BiC=BI-COLOR LED

LOWC=LOW CURRENT LED

YE=YELLOW

GR=GREEN

RD=RED

OR=ORANGE


NOTE:

THE TWO DIGITS PRECEDING THE
ADDITIONAL LED CODE MUST BE
USED IN THE PART NUMBER, WHEN
ORDERING ANY OF THE ADDITIONAL
LED OPTIONS.




UNLESS SPECIFIED OTHERWISE	DRAWN RONNIE.C	OCT29/21	Amphenol Canada Corp. Commercial Products		
PRIMARY UNITS MILLIMETERS	CHECKED KELVIN.T	OCT29/21			
SECONDARY INCHES	M.E. APP'D		VERTICAL MODULAR JACK SINGLE PORTS, 8 POSITION, 8 CONTACTS, WITH LED, SHIELDED, CAT.5e TRAY PACKAGING -RoHS COMPLIANT		
REFERENCE IN PARENTHESES	Q.A. APP'D				
GENERAL TOLERANCES	DWG APP'D		DWG NO. P-RJE44-188-1XX1		
1 DECIMAL PLACE	ENG. REL. NO.				
2 DECIMAL PLACES ±0.38	REF. EAR# RJ21060		REV B		
3 DECIMAL PLACES	THIRD ANGLE PROJECTION				
ANGULAR DEGREES			CODE ID NO. 03554	DWG SIZE X	SCALE N/A

REVISIONS			
REV	DESCRIPTION, ECN, EAR NO.	DATE	APP'D
A	NEW PROPOSAL	OCT29/21	L.CHAN
B	CORRECT THE LED POLARITIES	FEB07/23	KELVIN





TOP TRAY



BOTTOM TRAY




CONNECTORS



CARTON
(308*279*219 mm)

NOTES:

1. FINISHED CONNECTORS (AFTER FINAL INSPECTION) TO BE PACKED INTO CONDUCTIVE HIPS TRAYS, 80 CONNECTORS PER TRAY.
2. TOTAL 9 TRAYS LOADED WITH CONNECTORS TO BE PACKED INTO PE BAG, MUST SEAL PE BAG.
3. TRAYS & CARTONS MATERIAL MUST BE ABLE TO WITHSTAND IMPACT DURING PRODUCT TRANSPORTATION TO PREVENT ANY DAMAGE TO FINISHED CONNECTORS.
4. EACH TRAY AND CARTON OF PARTS TO BE LABELLED WITH AMPHENOL CANADA PART NUMBER, DATE CODE, QUANTITY, COUNTRY OF ORIGIN, AND CSA/UL LOGO WHEN APPROVED.



AMPHENOL P/N: RJE44-188-1XX1		Q' TY: 720
LOT#	DATE CODE	CTY OF ORIGIN: CN



THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.

UNLESS SPECIFIED OTHERWISE		DRAWN RONNIE.C		OCT29/21		Amphenol Canada Corp. Commercial Products							
PRIMARY UNITS MILLIMETERS		CHECKED KELVIN.T		OCT29/21									
SECONDARY INCHES		M.E. APP'D											
REFERENCE IN PARENTHESES		Q.A. APP'D											
GENERAL TOLERANCES		DWG APP'D											
1 DECIMAL PLACE		ENG. REL. NO.											
2 DECIMAL PLACES ±0.38		REF. EAR# RJ21060		DWG NO.									
3 DECIMAL PLACES		THIRD ANGLE PROJECTION		DO NOT SCALE DRAWING									
ANGULAR DEGREES				P-RJE44-188-1XX1									
				CODE ID NO. 0.3554		DWG SIZE X		SCALE N/A		SHEET 3 OF 3		REV B	