


6	5	4	3	2	1
ITEM	PART#	DESCRIPTION	QTY	UOM	
A	2147205000	Zero-Hachi 0.8 CRIMP TERM #28-30 SN	1	PC	



PART NUMBER	TITLE	CABLE DESCRIPTION	LENGTH'L'	CABLE COLOR
2196731121	Zero Hachi F-S 75mm 28 AWG BK Sn	1X28AWG DISC FEP BK UL10064	75±3	BLACK
2196731122	Zero Hachi F-S 150mm 28 AWG BK Sn	1X28AWG DISC FEP BK UL10064	150±4	BLACK
2196731123	Zero Hachi F-S 225mm 28 AWG BK Sn	1X28AWG DISC FEP BK UL10064	225±4	BLACK
2196731124	Zero Hachi F-S 300mm 28 AWG BK Sn	1X28AWG DISC FEP BK UL10064	300±4	BLACK
2196731125	Zero Hachi F-S 450mm 28 AWG BK Sn	1X28AWG DISC FEP BK UL10064	450±4	BLACK

- NOTES:
1. CRIMPING TO BE DONE AS PER MOLEX STANDARDS.
  2. THE PRODUCT SPECIFICATION RELIES ON THE TERMINALS & WIRE SPEC.
  - 3.FREE ENDS MUST BE STRIPPED,TWISTED &TINNED.THE LENGTH OF TINNING IS 5±1 MM.TINNING DIA MUST BE 0.45 MM MAX.
  - 4.TINNING SHOULD BE DONE WITH LEAD FREE SOLDER BAR ONLY.

REVISION			
DATE	REV	DESCRIPTION	CHANGER
2022/12/28	A	INITIAL RELEASE	THANUB
DOCUMENT STATUS	P1	RELEASE DATE	2023/01/19 11:41:22

<b>FUNCTIONAL SYMBOLS</b> = 0 = 0 = 0 <b>DIVISIONAL SYMBOLS</b>	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			
	<b>DIMENSION UNITS</b> <b>mm</b>	<b>SCALE</b> <b>NTS</b>	CURRENT REV DESC:	
	GENERAL TOLERANCES (UNLESS SPECIFIED)		EC NO: 734892	
	ANGULAR TOL ± °	4 PLACES ±	DRWN: THANUB	2022/11/03
3 PLACES ±	3 PLACES ±	CHK'D: SKUMAR07	2023/01/19	
2 PLACES ±	2 PLACES ±	APPR: SKUMAR07	2023/01/19	
1 PLACE ±	1 PLACE ±	INITIAL REVISION:		
0 PLACES ±	0 PLACES ±	DRWN: THANUB	2022/11/03	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION	DRAWING	SERIES
			A4-SIZE	219673
		MATERIAL NUMBER		CUSTOMER
		2196731121		GENERAL MARKET
		DOC TYPE		REVISION
		PSD		000
		DOC PART		A
		SHEET NUMBER		1 OF 1