


6		5		4		3	
ITEM	PART#	DESCRIPTION			QTY	UOM	
A	2078410004	RECEPTACLE HOUSING FOR L1NK 250 - 1X4 Ck			1	PC	
B	466261305	CRIMP TERMINAL FOR L1NK 250 - 22-24 AWG			4	PC	
C	--	WHITE PART ID LABEL			1	PC	

2		1	
FROM	TO	DESCRIPTION	COLOUR
A1	--	1X22AWG DISC PVC BK UL1569	BLACK
A2	--	1X22AWG DISC PVC BK UL1569	BLACK
A3	--	1X22AWG DISC PVC BK UL1569	BLACK
A4	--	1X22AWG DISC PVC BK UL1569	BLACK



PART NUMBER	TITLE	L1	L2(REF)
2240901040	KK Plus250 R-S 4ckt 50mm disc Sn	50±5	15
2240901041	KK Plus250 R-S 4ckt 100mm disc Sn	100±5	15
2240901042	KK Plus250 R-S 4ckt 150mm disc Sn	150±5	15
2240901043	KK Plus250 R-S 4ckt 300mm disc Sn	300±5	15
2240901044	KK Plus250 R-S 4ckt 600mm disc Sn	600±5	15

NOTES

- 1.THE PRODUCT MUST MEET PERFORMANCE SPECIFICATION AS PER ES-36586-004.
- 2.CONNECTOR VIEW SHOWN IS FROM MATING SIDE.
- 3.LABEL TEXT MUST BE 2 MM MAX. IN HEIGHT WITH ARIAL FONT.
- 4.LABEL MUST BE WRAPPED IN FLAG TYPE ON A SINGLE CABLE.
- 5.TINNING SHOULD BE DONE WITH LEAD FREE SOLDER BAR ONLY.
- 6.FREE ENDS MUST BE STRIPPED,TWISTED & TINNED.
- 7.THE LENGTH OF TINNING IS 5±1 MM.TINNING DIA MUST BE 1.0 MM MAX.

MOLEX P/N
MOLEX
BATCH WK/YR

DETAIL A

REVISION			
DATE	REV	DESCRIPTION	CHANGER
02/22/2023	B	INITIAL RELEASE	THANUB
RELEASE STATUS		P1	RELEASE DATE
			2023/03/23 11:04:44

FUNCTIONAL SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	
$\frac{F}{A} = 0$		DIMENSION UNITS	SCALE
$\frac{F}{E} = 0$		mm	NTS
$\frac{F}{P} = 0$		CURRENT REV DESC:	
DIVISIONAL SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)	
		ANGULAR TOL ± °	
		4 PLACES	±
		3 PLACES	±
		2 PLACES	±
		1 PLACE	±
		0 PLACES	±
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	
		THIRD ANGLE PROJECTION	DRAWING
		SERIES	MATERIAL NUMBER
		A4-SIZE	224090
		DOCUMENT NUMBER	CUSTOMER
		2240901040	GENERAL MARKET
		DOC TYPE	DOC PART
		PSD	000
		REVISION	B
		SHEET NUMBER	
		1 OF 1	