







REVISIONS					
REV	ECO	DESCRIPTION	DATE	BY	APPR
A1	--	RELEASED DRAWING	08/AUG/22	RONALD	TOMMY
A2	--	UPDATE THE PRODUCT NAME	27/OCT/22	LUCAS	TOMMY





PART NUMBER CHART	
COLOR	PART NUMBER
BLACK	ATS13-26Px-BM21
GREY	ATS13-26Px-BM21-GY
GREEN	ATS13-26Px-BM21-GN
BROWN	ATS13-26Px-BM21-BN



NOTES: UNLESS OTHERWISE SPECIFIED

- MATERIAL:
HOUSING: THERMOPLASTIC;
ARRANGEMENT PLATE: THERMOPLASTIC; COLOR:BLACK
CONTACT: COPPER ALLOY,GOLD PLATING
- SPECIFICATIONS:
2.1 CURRENT RATING: 7.5AMPS MAX
2.2 OPERATING TEMPERATURE: -55°C TO +125°C
2.3 DIELECTRIC WITHSTANDING VOLTAGE: LESS THAN 2 MILLIAMPS CURRENT LEAKAGE @ 1500 VOLTS AC.
2.4 INSULATION RESISTANCE: 1000 MEGOHMS MIN @ 25°C.
2.5 MOISTURE RESISTANCE: IP67&IP69K (MATED CONDITION)
2.6 MATING CYCLE DURABILITY: 500 MIN CYCLES
2.7 RoHS COMPLIANT
- MATING PART: ATS06-26Sx-* PLUG
(x = A,B KEYS ; * = ALL MODIFICATIONS)
- ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.



SEE P/N CHART		REF: 9-6437287-8, 9-6437287-9 (MATING INTERFACE ONLY)	
QUANTITY	PART NUMBER	DESCRIPTION	ITEM
MATERIALS LIST			
UNLESS OTHERWISE SPECIFIED 1) All dimensions are in metric(mm). 2) Tolerances are as follows: 1 PL DEC ±0.30 2 PL DEC ±0.15 3 PL DEC ±0.08 3) Note reference = x		SIGNATURES DATE DRAWN: LUCAS 27/OCT/22 CHECKED: ORION 30/OCT/22 ENGINEER: APPROVAL: TOMMY 31/OCT/22 CUSTOMER: THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.	Amphenol Sine Systems - www.amphenol-sine.com 44724 Morley Drive Clinton Township, MI 48036
MATERIAL SPECIFICATIONS: WEIGHT: 17.6g		26 POS, PCB RECEPTACLE, 3-HOLE FLANGE, PIN, ATS SERIES, RIGHT ANGLE	
PROCESS SPECIFICATIONS: NEXT ASSY:		SIZE B TYPE C- DWG NO: ATS13-26Px-BM21-xx SCALE: NONE	REVISION A2 SHEET 1 OF 1