

© 2023 TE Connectivity. All Rights Reserved.				REVISIONS				
P	LTR	DESCRIPTION			DATE	DWN	APVD	
	A	INITIAL VERSION			28SEP2023	F.Y	C.W	

D

D

C

C

B

B

A

A




NOTE:
1. TECHNICAL DATA SEE TABLE
2. MATERIAL SEE TABLE
3. THE PIN HOLES WITHOUT CONTACTS USE 2473754-3 FOR SEALING
4. APPICABLE TERMINAL PART NUMBER AND WIRE SIZE AND SINGLE WIRE SEAL SEE TABLE 2


技术要求：
1. 技术参数参见表1
2. 材质见表2
3. 未装针的PIN孔可用2473754-3堵头来封堵
4. 适用端子与导线尺寸以及单线密封件参考表2

TABLE 2					
T2210002010-041	TIN	0.50~0.75mm ² 20AWG~18AWG	Ø1.40-Ø1.90	2473754-1	2473754-3 (OPTION)
T2210002010-040	GOLD				
T2210002010-031	TIN	0.20~0.35mm ² 24AWG~22AWG	Ø1.10-Ø1.40	2473754-2	
T2210002010-030	GOLD				
TERMINAL PN	TERMINAL PLATING	WIRE SIZE (mm ²)	INSULATION WIRES(MM)	SINGLE WIRE SEAL PN	BLIND PLUG PN

TECHNICAL DATA (TABLE 1)	2469979-00X
RATED VOLTAGE	63V
RATED CURRENT	5A MAX.
POLLUTION DEGREE	3
OVERVOLTAGE CATEGORY	II
INSULATION RESISTANCE	≥100MΩ
DEGREE OF PROTECTION	IP67

RUBBER	O-RING	3	1
PBT	PROTECTION COVER	2	1
PBT	FEMALE HOUSING	1	1
MATERIAL	DESCRIPTION	ITEM	2469979-00X

			KEYING TYPE
2469979-1	2469979-2	2469979-3	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 28SEP2023 FENCER YU	 TE Connectivity			
DIMENSIONS: mm		CHK 28SEP2023 CHRIS WANG				
		APVD 28SEP2023 CHRIS WANG	NAME EASYLOCK PLASTIC SIGNAL CONNECTOR FEMALE, 8 POLES			
		PRODUCT SPEC 108-137685	-			
MATERIAL SEE NOTE		APPLICATION SPEC 114-137685	SIZE A2	CAGE CODE 00779	DRAWING NO C-2469979	RESTRICTED TO -
		WEIGHT -	CUSTOMER DRAWING		SCALE 2:1	SHEET 1 OF 1
						REV A