






REVISIONS					
REV	ECO	DESCRIPTION	DATE	BY	APPR
A1	--	RELEASED DRAWING	08/AUG/22	RONALD	TOMMY
A2	--	UPDATE THE PRODUCT NAME	27/OCT/22	LUCAS	TOMMY



INTERNAL SEALING SURFACE
FINISH TO BE 3.2/ OR BETTER 0.13




1.7 5.5
THICKNESS

RECOMMENDED PANEL CUTOUT



DETAIL "F"


PART NUMBER CHART	
COLOR	PART NUMBER
BLACK	ATS15-26Px-BM01
GREY	ATS15-26Px-BM01-GY
GREEN	ATS15-26Px-BM01-GN
BROWN	ATS15-26Px-BM01-BN



RECOMMENDED PCB LAYOUT

NOTES: UNLESS OTHERWISE SPECIFIED

- MATERIAL:
HOUSING: THERMOPLASTIC;
CONTACT: COPPER ALLOY,GOLD PLATING
SEAL: SILICONE RUBBER
- SPECIFICATIONS:
2.1 CURRENT RATING: 7.5AMPS MAX
2.2 OPERATING TEMPERATURE: -55°C TO +125°C
2.3 DIELECTRIC WITHSTANDING VOLTAGE: LESS THAN 2 MILLIAMPS CURRENT LEAKAGE @ 1500 VOLTS AC.
2.4 INSULATION RESISTANCE: 1000 MEGOHMS MIN @ 25°C.
2.5 MOISTURE RESISTANCE: IP67&IP69K (MATED CONDITION)
2.6 MATING CYCLE DURABILITY: 500 MIN CYCLES
2.7 RoHS COMPLIANT
- MATING PART: ATS06-26Sx-* PLUG
(x = A,B KEYS ; * = ALL MODIFICATIONS)
- ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.



SEE P/N CHART		REF: 6437288-6, 6473418-1 (MATING INTERFACE ONLY)	
QUANTITY	PART NUMBER	DESCRIPTION	ITEM
MATERIALS LIST			
UNLESS OTHERWISE SPECIFIED		SIGNATURES	DATE
1) All dimensions are in metric(mm). 2) Tolerances are as follows: 1 PL DEC ±0.30 2 PL DEC ±0.15 3 PL DEC ±0.08 3) Note reference = X		DRAWN: LUCAS	27/OCT/22
		CHECKED: ORION	30/OCT/22
		ENGINEER:	
		APPROVAL: TOMMY	31/OCT/22
MATERIAL SPECIFICATIONS:		CUSTOMER:	
WEIGHT: 16.2g		THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.	
PROCESS SPECIFICATIONS:			
NEXT ASSY:			
		26 POS, PCB RECEPTACLE WITH FLANGE, PIN, ATS SERIES, PANEL, STRAIGHT	
SIZE B		DWG NO: ATS15-26Px-BM01-xx	
TYPE C-		REVISION A2	
SCALE: NONE		SHEET 1 OF 1	

TITLE: 26 POS, PCB RECEPT W/ FLANGE, PIN, ATS SERIES, PANEL, STRAIGHT

DWG NO:

ATS15-26Px-BM01-xx

REV: A2

SH: 1

OF: 1