


6		5		4	
ITEM	PART#	DESCRIPTION		QTY	UOM
A,B	347910040	MINI50 CONN RCPT 4CKT NB BLK POL A		2	PC
C	5600230421	CTX50 RCPT TERM SN M-GRIP D WIND		8	PC
D	--	WHITE PART ID LABEL		1	PC

2		1	
FROM	TO	DESCRIPTION	COLOUR
A1	B1	1X0.22 SQMM DISC PVC BK FLRYW125	BLACK
A2	B2	1X0.22 SQMM DISC PVC BK FLRYW125	BLACK
A3	B3	1X0.22 SQMM DISC PVC BK FLRYW125	BLACK
A4	B4	1X0.22 SQMM DISC PVC BK FLRYW125	BLACK



PART NUMBER	TITLE	L1	L2(REF)
2240501042	Mini50 R-R 4ckt 150mm disc Sn	150±5	15
2240501043	Mini50 R-R 4ckt 300mm disc Sn	300±5	15
2240501044	Mini50 R-R 4ckt 600mm disc Sn	600±5	15

MOLEX P/N
MOLEX
BATCH WK/YR

DETAIL A

NOTES

1. CABLE ASSEMBLY TO BE TESTED 100% FOR CONTINUITY AND POLARITY.
2. CONNECTOR VIEW SHOWN IS FROM MATING SIDE.
- 3.LABEL TEXT MUST BE 2 MM MAX. IN HEIGHT WITH ARIAL FONT.
- 4.LABEL MUST BE WRAPPED IN FLAG TYPE ON A SINGLE CABLE.

REVISION			
DATE	REV	DESCRIPTION	CHANGER
03/30/2023	A	INITIAL RELEASE	THANUB
RELEASE STATUS		P1	RELEASE DATE
			2023/05/18 06:16:26

FUNCTIONAL SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	
$\frac{F}{A} = 0$	DIMENSION UNITS	SCALE	CURRENT REV DESC:
$\frac{F}{E} = 0$	mm	NTS	
$\frac{F}{P} = 0$	GENERAL TOLERANCES (UNLESS SPECIFIED)		
	ANGULAR TOL ± °		
	4 PLACES	±	EC NO: 749372
	3 PLACES	±	DRWN: THANUB 2023/04/18
	2 PLACES	±	CHK'D: SKUMAR07 2023/05/18
	1 PLACE	±	APPR: SKUMAR07 2023/05/18
	0 PLACES	±	INITIAL REVISION:
			DRWN: THANUB 2023/03/30
			APPR: SKUMAR07 2023/04/05
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION
			DRAWING
			SERIES
			MATERIAL NUMBER
			CUSTOMER
			SHEET NUMBER

molex

SEE TABLE

PRODUCT CUSTOMER DRAWING

DOCUMENT NUMBER	DOC TYPE	DOC PART	REVISION
2240501042	PSD	000	B

SEE TABLE	GENERAL MARKET	1 OF 1
-----------	----------------	--------