

10		9		8		7	
ITEM	MOLEX P/N	DESCRIPTION				QTY	UOM
A	50375023	2.5 Low Profile Hsg 2Ckt 5264-02				1	PC
B	8701039	2.5 Low Profile Crimp Rec Term 5263PBT				2	PC
PL	-	PART IDENTIFICATION LABEL				1	PC

3		2		1
FROM	TO	WIRE SIZE	WIRE TYPE	COLOR
A1	-	22 AWG	UL 1569	BLACK
A2	-	22 AWG	UL 1569	BLACK




TABLE			
FG PART #	L1	L2 (REF)	TITLE
2264311022	150±4	65	Mini-Spox R-S 2ckt 150mm disc Sn
2264311023	300±4	140	Mini-Spox R-S 2ckt 300mm disc Sn
2264311024	600±6	290	Mini-Spox R-S 2ckt 600mm disc Sn

NOTE:

1. CABLE ASSEMBLY MUST PASS 100% CONTINUITY AND POLARITY TEST
2. CONNECTOR VIEW IS SHOWN FROM MATING SIDE
3. LABEL TEXT MUST BE 2MM MAX IN HEIGHT WITH ARIAL FONT AND WRAPPED IN FLAG TYPE ON A SINGLE WIRE.
4. THE PRODUCT HAS TO MEET PERFORMANCE SPECIFICATION AS PER ES-36586-004
5. FREE ENDS MUST BE STRIPPED, TWISTED & TINNED. THE LENGTH OF TINNING IS 5 ± 1 MM. TINNING DIA MUST BE 1 MM MAX.

MOLEX PN
MOLEX
BATCH WK/YR

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
FUNCTIONAL SYMBOLS		DIMENSION UNITS		SCALE		CURRENT REV DESC:			
$\frac{E}{A} = 0$		mm		NTS		EC NO: 775088 DRWN: CHIDAG12023/12/29 CHK'D: SKUMAR072024/01/25 APPR: SKUMAR072024/01/25 INITIAL REVISION: DRWN: CHIDAG12023/12/29 APPR: SKUMAR072024/01/25			
$\frac{E}{E} = 0$		GENERAL TOLERANCES (UNLESS SPECIFIED)							
$\frac{E}{E} = 0$		ANGULAR TOL. ± °							
DIVISIONAL SYMBOLS		4 PLACES ±							
		3 PLACES ±				SEE TABLE			
		2 PLACES ±							
		1 PLACE ±				PRODUCT CUSTOMER DRAWING			
		0 PLACES ±							
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		DRAWING		SERIES	
						A3-SIZE		226431	
						MATERIAL NUMBER		CUSTOMER	
						SEE TABLE		GENERAL MARKET	
								SHEET NUMBER	
								1 OF 1	

DOCUMENT STATUS	P1	RELEASE DATE	2024/01/25	04:39:23
-----------------	----	--------------	------------	----------