








AS SHOWN : 2390404-1(W KEY)

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASED	08NOV2021	H.O	T.S



SCALE 1:2



1. GENERAL TOLERANCES: SEE FOLLOWS
0.00- 9.00 : ± 0.3
10.00-19.00 : ± 0.4
20.00-29.00 : ± 0.5
30.00- : ± 0.6
2. THE SHAPE, SIZE AND POSITION OF THE CHARACTER SHOW THE OUTLINE. THEY DON'T SHOW DETAILS.
3. PANEL ATTACHMENT RECOMMENDATION SCREW: M3

W	1	GLASS FILED THERMO PLASTIC (94V-0), COLOR:BLACK	PANEL FRAME HSG (W)	5
	2	STEEL	FRAME LOCK PLATE	4
	2	GLASS FILED THERMO PLASTIC (94V-0), COLOR:BLACK	SHIFT LEVER	3
	2	STEEL	SPRING PIN	2
	2	STEEL	TWIST SPRING	1
KEY	2390404-1	MATERIAL	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN H.OSABE 01NOV2021		
		CHK T.SHIMOYASU 01NOV2021		
		APVD T.SHIMOYASU 01NOV2021	NAME DYNAMIC HIGH DENSITY FRAME PANEL FRAME ASSEMBLY 2 MODULES	
		PRODUCT SPEC 108-78644		
		APPLICATION SPEC -		
		WEIGHT 32.74 g	SIZE A3	CAGE CODE 00779
		CUSTOMER DRAWING	SCALE 1:1	SHEET 1 OF 1
				REV A