


REV	DOCUMENT	CHANGED BY	CHECK
4	0038444	KVS 09APR08	ASD



RELEASE NO.	SR - 11177
REPLACES	

CHARACTERISTICS		ELECTRICAL DATA				DESIGN UNITS: INCH				DRAWN	VK	18 FEB 08		Honeywell							
OPERATING FORCE — — — - 3 - 5 OZ		CONTACT ARRANGEMENT S P D T				TOLERANCES UNLESS NOTED: NO PLACE X ± ONE PLACE .X ± 0.030 TWO PLACE .XX ± 0.015 THREE PLACE .XXX ± 0.005 FOUR PLACE .XXXX ± ANGLES ± THIRD ANGLE PROJECTION 				CHECK	RJ	18 FEB 08								TITLE SWITCH - BASIC	
RELEASE FORCE— — — — - 1 OZ MIN		30 VOLTS DC RATING								THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.											
DIFFERENTIAL TRAVEL— — - .004 MAX		SEA LEVEL 50,000 FT														INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY					
OVERTRAVEL — — — — - .005 MIN		LOAD	28 VDC	115 VAC 60 CPS	28 VDC					SIZE	TYPE	DRAWING NAME		REV							
RESISTIVE	5.0 AMP	5.0 AMP	5.0 AMP	B	I					21SM284		4									
INDUCTIVE	3.0 AMP	5.0 AMP	2.5 AMP																		
LAMP	2.4 AMP	1.5 AMP	2.4 AMP							SCALE	-	WEIGHT .006 LB MAX	SHEET 1 OF 1								
										RASTER											

21SM284 04 Released Honewell proprietary & Confidential A