




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	GTP(ECN-23-229101)	01SEP2023	ED	WH



RECOMMENDED MOUNTING HOLE



PCB MOUNTING HOLE

NOTES:

- 1 PACK IN ACCORDANCE WITH TE SPEC 107-3275;
- 2 ALL DIMENSIONS ARE NOMINAL FOR REFERENCE ONLY UNLESS OTHERWISE STATED;
- 3 ELECTRICAL CHARACTERISTICS :
FREQUENCY RANGE : DC-12GHz
NOMINAL IMPEDANCE : 75 OHMS
INSULATION RESISTANCE : 1000 MOHMS
WORKING VOLTAGE : 335 VRMS MAX
DIELECTRIC WITHSTANDING VOLTAGE : 1000 VOLTS MAX
Return Loss : 17dB MAX (DC-12GHz)
CONTACT RESISTANCE :
CENTER CONTACT : 5 mOHMS MAX
OUTER CONTACT : 2.5 mOHMS MAX;
- 4 MECHANICAL CHARACTERISTICS :
DURABILITY : 500 CYCLES;
- 5 TEMPERATURE RANGE: -55°-+125°;
- 6 RoHS: COMPLIANT;
- 7 MAX. PANEL THICKNESS=2.2mm;

- 8 NICKEL PLATING 100u" MIN OVER COPPER PLATING;
- 9 GOLD PLATING 3u" MIN OVER NICKEL PLATING OVER COPPER PLATING;
- 10 GOLD PLATING 10u" MIN OVER NICKEL PLATING OVER COPPER PLATING;
- 11 GOLD PLATING 1u" MIN OVER NICKEL PLATING OVER COPPER PLATING;
- 12 GOLD PLATING 30u" MIN OVER NICKEL PLATING OVER COPPER PLATING.

1	8	1	8	1	8	BRASS	NUT	5
1	8	1	8	1	8	BRASS	LOCK WSHR	4
1	12	1	10	1	9	BERYLLIUM COPPER	CONTACT PIN	3
1		1		1		PTFE,NATURAL	INSULATOR	2
1	12	1	10	1	11	BRASS	BODY	1
2446153-3		2446153-2		2446153-1		MATERIAL	DESCRIPTION	ITEM
QUANTITY PER ASSY						PARTS LIST		

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN	ED	24APR2023	 TE Connectivity							
			CHK	RZ	24APR2023								
DIMENSIONS:			TOLERANCES UNLESS OTHERWISE SPECIFIED:			NAME HIGH DENSITY BNC MOUNT JACK,PCB, BULKHEAD,DC-12GHZ -							
mm													
			0 PLC ± 0.3							SIZE			
			1 PLC ± 0.2										
			2 PLC ± 0.1			CAGE CODE							
			3 PLC ± -										
			4 PLC ± -			DRAWING NO							
			ANGLES ± 5°										
MATERIAL			FINISH			RESTRICTED TO							
-			-										
			WEIGHT			A2 00779 C=2446153							
			0										
			CUSTOMER DRAWING			SCALE							
						SHEET							
						1 OF 1							
						REV							
						A							