





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	GTP(ECN-23-229280)	02SEP2023	ED	WH



NOTES:

- PACK IN ACCORDANCE WITH TE SPEC 107-3275;
- ALL DIMENSIONS ARE NOMINAL FOR REFERENCE ONLY UNLESS OTHERWISE STATED;
- ELECTRICAL CHARACTERISTICS :
FREQUENCY RANGE : DC-12GHz
NOMINAL IMPEDANCE : 75 OHMS
INSULATION RESISTANCE : 1000 MOHMS
WORKING VOLTAGE : 335 VRMS MAX
DIELECTRIC WITHSTANDING VOLTAGE : 1000 VOLTS MAX
Return Loss : 17dB MAX (DC-12GHz)
CONTACT RESISTANCE :
CENTER CONTACT : 5 mOHMS MAX
OUTER CONTACT : 2.5 mOHMS MAX;
- MECHANICAL CHARACTERISTICS :
DURABILITY : 500 CYCLES;
- TEMPERATURE RANGE: -55°-+125°;
- RoHS: COMPLIANT;
- MAX. PANEL THICKNESS=2.2mm;

- 8 NICKEL PLATING 100u" MIN OVER COPPER PLATING;
- 9 GOLD PLATING 3u" MIN OVER NICKEL PLATING OVER COPPER PLATING;
- 10 GOLD PLATING 10u" MIN OVER NICKEL PLATING OVER COPPER PLATING;
- 11 GOLD PLATING 1u" MIN OVER NICKEL PLATING OVER COPPER PLATING;
- 12 GOLD PLATING 30u" MIN OVER NICKEL PLATING OVER COPPER PLATING.



1	8	1	8	1	8	BRASS	NUT	5
1	8	1	8	1	8	BRASS	LOCK WSHR	4
1	12	1	10	1	9	BERYLLIUM COPPER	CONTACT PIN	3
1		1		1		PTFE,NATURAL	INSULATOR	2
1	12	1	10	1	11	BRASS	BODY	1
2446156-3	2446156-2	2446156-1				MATERIAL	DESCRIPTION	ITEM
QUANTITY PER ASSY			PARTS LIST					

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN ED	24APR2023	 TE Connectivity				
			CHK RZ	24APR2023					
			APVD WH	24APR2023					
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC	NAME HIGH DENSITY BNC MOUNT JACK,END LAUNCH, BULKHEAD,DC-12GHZ				
		0 PLC ± 0.3		—					
		1 PLC ± 0.2		—					
		2 PLC ± 0.1		—					
		3 PLC ± —		APPLICATION SPEC					
		4 PLC ± —		—					
ANGLES ± 5°				—	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
MATERIAL —		FINISH —		WEIGHT 0	A2	00779	C=2446156	—	
CUSTOMER DRAWING					SCALE 1		SHEET 1 of 1		REV A