



1	2	3	4																																
A				A																															
B	<table border="1" data-bbox="1037 627 1340 761"><thead><tr><th>Part No.</th><th>Cable color</th></tr></thead><tbody><tr><td>~04*1TV~</td><td>WHITE</td></tr><tr><td>~04*2TV~</td><td>BLACK</td></tr></tbody></table>			Part No.	Cable color	~04*1TV~	WHITE	~04*2TV~	BLACK	B																									
Part No.	Cable color																																		
~04*1TV~	WHITE																																		
~04*2TV~	BLACK																																		
C	NOTE ① We indicate the length of the harness on the last of product name, 'L' part. ② Tolerance for [L] <table border="1" data-bbox="446 1030 1069 1232"><thead><tr><th>Length L [mm]</th><th>Tolerance [mm]</th></tr></thead><tbody><tr><td>$35 \leq L \leq 200$</td><td>± 4</td></tr><tr><td>$200 < L \leq 500$</td><td>± 8</td></tr><tr><td>$500 < L \leq 1000$</td><td>± 12</td></tr><tr><td>$1000 < L$</td><td>$\pm 1.5\%$</td></tr></tbody></table>			Length L [mm]	Tolerance [mm]	$35 \leq L \leq 200$	± 4	$200 < L \leq 500$	± 8	$500 < L \leq 1000$	± 12	$1000 < L$	$\pm 1.5\%$	C																					
Length L [mm]	Tolerance [mm]																																		
$35 \leq L \leq 200$	± 4																																		
$200 < L \leq 500$	± 8																																		
$500 < L \leq 1000$	± 12																																		
$1000 < L$	$\pm 1.5\%$																																		
D	③ Connector rotation angle is within ± 45 degree from the above image. For long length in the case of $L > 500$, the angle is optional. 4. Specifications are subject to change without notice. 【 DIMENSIONS OF CONNECTOR 】 			D																															
E	<table border="1" data-bbox="175 1859 1500 1948"><thead><tr><th>1</th><th>U.FL-LP-040HF</th><th>CL331-0557-3</th><th>2</th><th>0.81 Dia. coaxial cable</th><th>HALOGEN FREE</th></tr><tr><th>NO.</th><th>PART NO.</th><th>CODE NO.</th><th>NO.</th><th>PART NO.</th><th></th></tr></thead></table>			1	U.FL-LP-040HF	CL331-0557-3	2	0.81 Dia. coaxial cable	HALOGEN FREE	NO.	PART NO.	CODE NO.	NO.	PART NO.		E																			
1	U.FL-LP-040HF	CL331-0557-3	2	0.81 Dia. coaxial cable	HALOGEN FREE																														
NO.	PART NO.	CODE NO.	NO.	PART NO.																															
F	<table border="1" data-bbox="175 1948 1500 2150"><thead><tr><th>UNITS mm</th><th>SCALE FREE</th><th>COUNT</th><th>DESCRIPTION OF REVISIONS</th><th>DESIGNED</th><th>CHECKED</th><th>DATE</th></tr></thead><tbody><tr><td rowspan="4"></td><td rowspan="4">HIROSE ELECTRIC CO., LTD.</td><td>APPROVED</td><td>・TS. NOBE</td><td>18.06.18</td><td colspan="2">DRAWING NO.</td></tr><tr><td>CHECKED</td><td>・MT. KANEKO</td><td>18.06.18</td><td colspan="2">PART NO.</td></tr><tr><td>DESIGNED</td><td>・MS. MATSUMOTO</td><td>18.06.18</td><td colspan="2">U. FL-2LPHF6-04**TV-A-L ①</td></tr><tr><td>DRAWN</td><td>・MS. MATSUMOTO</td><td>18.06.18</td><td colspan="2">CODE NO.</td></tr></tbody></table>					UNITS mm	SCALE FREE	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE		HIROSE ELECTRIC CO., LTD.	APPROVED	・TS. NOBE	18.06.18	DRAWING NO.		CHECKED	・MT. KANEKO	18.06.18	PART NO.		DESIGNED	・MS. MATSUMOTO	18.06.18	U. FL-2LPHF6-04**TV-A-L ①		DRAWN	・MS. MATSUMOTO	18.06.18	CODE NO.		F
UNITS mm	SCALE FREE	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE																													
	HIROSE ELECTRIC CO., LTD.	APPROVED	・TS. NOBE	18.06.18	DRAWING NO.																														
		CHECKED	・MT. KANEKO	18.06.18	PART NO.																														
		DESIGNED	・MS. MATSUMOTO	18.06.18	U. FL-2LPHF6-04**TV-A-L ①																														
		DRAWN	・MS. MATSUMOTO	18.06.18	CODE NO.																														