


ITEM	PART#	DESCRIPTION	QTY	UOM
A	2140935000	OneBlade 1.0WB CRIMP TERM SN AWG 28-30	1	PC



PART NUMBER	TITLE	CABLE DESCRIPTION	LENGTH 'L'	CABLE COLOR
2196752121	One Blade F-S 75mm 28 AWG RD Sn	1X28AWG DISC ETFE RD UL10125	75±3	RED
2196752122	One Blade F-S 150mm 28 AWG RD Sn	1X28AWG DISC ETFE RD UL10125	150±4	RED
2196752123	One Blade F-S 225mm 28 AWG RD Sn	1X28AWG DISC ETFE RD UL10125	225±4	RED
2196752124	One Blade F-S 300mm 28 AWG RD Sn	1X28AWG DISC ETFE RD UL10125	300±4	RED
2196752125	One Blade F-S 450mm 28 AWG RD Sn	1X28AWG DISC ETFE RD UL10125	450±4	RED

NOTES:

1. CRIMPING TO BE DONE AS PER MOLEX STANDARDS.
2. THE PRODUCT SPECIFICATION RELIES ON THE TERMINALS & WIRE SPEC.
- 3.FREE ENDS MUST BE STRIPPED,TWISTED &TINNED.THE LENGTH OF TINNING IS 5±1 MM.TINNING DIA MUST BE 0.45 MM MAX.
- 4.ONLY LEAD FREE SOLDER BAR TO USED.

REVISION				
DATE	REV	DESCRIPTION	CHANGER	
2022/12/28	A	INITIAL RELEASE	THANUB	
DOCUMENT STATUS	P1	RELEASE DATE	2023/01/19	11:45:13

FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION														
	DIMENSION UNITS		SCALE		CURRENT REV DESC:			molex							
	mm		NTS												
	GENERAL TOLERANCES (UNLESS SPECIFIED)							SEE TABLE							
	ANGULAR TOL ± °														
	4 PLACES		±		EC NO: 734899			PRODUCT CUSTOMER DRAWING							
	3 PLACES		±		DRWN: THANUB 2022/12/29										
	2 PLACES		±		CHK'D: SKUMAR07 2023/01/19										
	1 PLACE		±		APPR: SKUMAR07 2023/01/19										
	0 PLACES		±		INITIAL REVISION:										
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		DRAWING		SERIES					DOCUMENT NUMBER		DOC TYPE	DOC PART	REVISION
											2196752121		PSD	000	A
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		DRAWING		SERIES					MATERIAL NUMBER		CUSTOMER		SHEET NUMBER
											SEE TABLE		GENERAL MARKET		1 OF 1