




REV	DESCRIPTION\PER REQUEST	DRAWN	DATE
D	UPDATE REV ECO-14519	DCam	11/10/21

CRIMP SIZES REQUIRED
CONTACT: SQ.042(1.06mm), CRIMP TOOL KTH-6001
FERRULE: HEX.255(6.48mm)

PATENT PENDING



RECOMMENDED
CABLE STRIPPING DIM'S



CABLE:BELDEN 1505A

10	FERRULE	1	BRASS	NICKEL
9	SHELL	1	BRASS	NICKEL
8	GASKET	1	SI-RUBBER	BLACK
7	RETAINING RING	1	BRASS	NICKEL
6	SPRING	1	STEEL	NICKEL
5	WASHER	1	BRASS	NICKEL
4	INSULATOR	1	PTFE	NATURAL
3	PIN	1	PHOS BRONZE	GOLD
2	BODY	1	BECU	NICKEL
1	BODY	1	BRASS	NICKEL
NO	DESCRIPTION/DRAWING NO.	Q'TY	MATERIAL	FINISH

PART NO.	HHD1505A
APPROVED	DATE 02/07/14
CHECKED	DATE 02/07/14
DRAWN	DATE 02/07/14
	Kdi

* MAJOR DIMENSION	UNLESS OTHERWISE NOTED TOLERANCES 0.5-6=±0.2 6-30=±0.4 30-120=±0.6 120-315=±1.0 ANGLES=±5°
Bomar Interconnect Products,Inc	TITLE HDBNC CRIMP PLUG
DRAWING NO. ASHDBNC-41004-G1-75-TGN	REV D
FILE NO. W:\77\AS\ASHDBNC\ASHDBNC-41004-G1-75-TGN	Winchester-->20140604

