





| REV | DESCRIPTION\PER REQUEST | DRAWN | DATE |
|-----|-------------------------|-------|------|
|     |                         |       |      |
|     |                         |       |      |

CRIMP SIZES REQUIRED  
CONTACT: SQ.042(1.06mm), CRIMP TOOL KTH-6001  
FERRULE: HEX.178(4.52mm)



RECOMMENDED  
CABLE STRIPPING DIM'S

PATENT PENDING



CABLE:BELDEN 1855A

|    |                         |      |             |         |
|----|-------------------------|------|-------------|---------|
| 10 | FERRULE                 | 1    | BRASS       | NICKEL  |
| 9  | SHELL                   | 1    | BRASS       | NICKEL  |
| 8  | GASKET                  | 1    | SI-RUBBER   | BLACK   |
| 7  | RETAINING RING          | 1    | BRASS       | NICKEL  |
| 6  | SPRING                  | 1    | STEEL       | NICKEL  |
| 5  | WASHER                  | 1    | BRASS       | NICKEL  |
| 4  | INSULATOR               | 1    | PTFE        | NATURAL |
| 3  | PIN                     | 1    | PHOS BRONZE | GOLD    |
| 2  | BODY                    | 1    | BECU        | NICKEL  |
| 1  | BODY                    | 1    | BRASS       | NICKEL  |
| NO | DESCRIPTION/DRAWING NO. | Q'TY | MATERIAL    | FINISH  |

|          |               |
|----------|---------------|
| PART NO. | HDD1855A      |
| APPROVED | DATE 02/07/14 |
| CHECKED  | DATE 02/07/14 |
| DRAWN    | DATE 02/07/14 |
|          | Kdi           |

|                                                                        |     |      |                                                                                                           |  |
|------------------------------------------------------------------------|-----|------|-----------------------------------------------------------------------------------------------------------|--|
| * MAJOR DIMENSION                                                      |     |      | UNLESS OTHERWISE NOTED TOLERANCES<br>0.5-6=±0.2<br>6-30=±0.4<br>30-120=±0.6<br>120-315=±1.0<br>ANGLES=±5° |  |
| SCALE                                                                  | 4/1 | UNIT | mm                                                                                                        |  |
| Bomar Interconnect Products, Inc                                       |     |      |                                                                                                           |  |
| TITLE<br>HDBNC CRIMP PLUG                                              |     |      |                                                                                                           |  |
| DRAWING NO.<br>ASHDBNC-41004-G-75-TGN                                  |     |      | REV C                                                                                                     |  |
| FILE NO. W:\77-\AS\ASHDBNC\ASHDBNC-41004-G-75-TGN Winchester->20140604 |     |      |                                                                                                           |  |

H0HC1V001-000