


NOTES: UNLESS OTHERWISE SPECIFIED


1. FOR USE WITH BELDEN 9529, 1505A & 1805F CABLES.
2. FOR CABLING INSTRUCTIONS SEE 3-661-1.
3. FOR CRIMPING USE DIE KTH-2261.
4. INTERFACE PER KINGS ES-17, FIG. 6
5. MATERIAL SPECIFICATIONS:
INSULATOR: TEFLON, ASTM-D-4894 OR ASTM D1710
GASKET: SILICONE RUBBER, A-A-59588
SPRING WASHER, OUTER CONTACT: BERYLLIUM COPPER PER ASTM B196
K-GRIP SLEEVE: COMMERCIAL BRONZE, ASTM B135
ALL OTHER METAL PARTS: BRASS PER ASTM B16
6. FINISH SPECIFICATIONS:
CENTER CONTACT: GOLD PLATE PER ASTM B488
SRING WASHER: SILVER PLATE PER ASTM B700 OR NICKEL PLATE PER SAE AMS-QQ-N-290
ALL OTHER METAL PARTS:NICKEL PLATE PER SAE AMS-QQ-N-290
7. ELECTRICAL SPECIFICATIONS:
IMPEDANCE: 75 OHMS
WORKING VOLTAGE: 500 VOLTS RMS
FREQUENCY RANGE: DC - 12 GHz
RETURN LOSS: -30dB MAX TO 3.0 GHz
-20dB MAX TO 6.0 GHz
8. COMPLIANT TO 3G/6G/12G SDI SMPTE REQUIREMENTS.

REV	DESCRIPTION	BY	DATE	APPD
P	ER057798	J	04/10/15	YA
U	UPDATED PER ECO-15015	AV	05/03/22	DCom



MARK: KINGS 2065-2-9 (DATE CODE)

CATALOG P/N: 2065-2-9



PER ASME Y14.5M-1994 UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN INCHES (MM) TOLERANCES: DECIMAL: .XX [X.X] ± .01 [0.25] .XXX [X.XX] ± .004 [0.10] .XXXX [X.XXX] ± .XXXX ANGLES: ± 2° SCALE: 4:1				Winchester 68 Water St. Interconnect. Norwalk, CT 06854			
CUSTOMER SALES DRAWING				75 OHM BNC PLUG FOR BELDEN 1505A OR EQUIVALENT CABLE (RoHS)			
DRAWN	DATE	APPROVED	DATE	THIRD ANGLE	SD2065-2-9		
APPROVED	DATE	APPROVED	DATE		SHT	OF	REV
XX/XX/XX	XX/XX/XX	XX/XX/XX	XX/XX/XX		1	1	U

This document may be out-of-date because it has file references that may have been updated. (more...)