

10

9

8

7

6

5

4

3

2

1

ITEM	MOLEX P/N	DESCRIPTION	QTY	UOM							FROM	TO	WIRE SIZE	WIRE TYPE	COLOR				
A	2147192060	Zero-Hachi 0.8 CRIMP HSG SR BK 6P	1	PC							A1	--	28 AWG	UL 10064	BLACK				
B	2147205000	Zero-Hachi 0.8 CRIMP TERM #28-30 SN	6	PC							A2	--	28 AWG	UL 10064	BLACK				
PL	--	PART IDENTIFICATION LABEL	1	PC							A3	--	28 AWG	UL 10064	BLACK				
															A4	--	28 AWG	UL 10064	BLACK
															A5	--	28 AWG	UL 10064	BLACK
															A6	--	28 AWG	UL 10064	BLACK

Technical drawing of a cable assembly. The drawing includes a side view of the cable with dimensions L1 and (L2). A detail view labeled 'DETAIL A' shows the connector and label. A table below the drawing lists part numbers, lengths, and titles. A note at the bottom left provides instructions. A table at the bottom right contains functional symbols and drawing information.

TABLE			
FG PART #	L1	L2 (REF)	TITLE
2263921062	150±4	63	Zero-Hachi BI R-S 6ckt 150mm disc Sn
2263921063	300±4	138	Zero-Hachi BI R-S 6ckt 300mm disc Sn
2263921064	600±4	288	Zero-Hachi BI R-S 6ckt 600mm disc Sn

NOTE:

- CABLE ASSEMBLY MUST PASS 100% CONTINUITY AND POLARITY TEST
- CONNECTOR VIEW IS SHOWN FROM MATING SIDE
- LABEL TEXT MUST BE 2MM MAX IN HEIGHT WITH ARIAL FONT AND WRAPPED IN FLAG TYPE ON A SINGLE WIRE.
- THE PRODUCT HAS TO MEET PERFORMANCE SPECIFICATION AS PER ES-36586-004
- FREE ENDS MUST BE STRIPPED, TWISTED & TINNED. THE LENGTH OF TINNING IS 5±1MM. TINNING DIA MUST BE 0.45MM MAX.

FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						
	DIMENSION UNITS	SCALE					
	mm	NTS					
	GENERAL TOLERANCES (UNLESS SPECIFIED)						
DIVISIONAL SYMBOLS	ANGULAR TOL	± °					
	4 PLACES	±					
	3 PLACES	±					
	2 PLACES	±					
	1 PLACE	±					
	0 PLACES	±					
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION	DRAWING	SERIES	MATERIAL NUMBER	CUSTOMER	SHEET NUMBER
			A3-SIZE	226392	SEE TABLE	GENERAL MARKET	1 OF 1