



REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	D	REVISED PER E.O. P20392	03DEC2009		RDR
	E	REVISED PER PCN E-18-007949	23MAY2018	DD	DM
	F	REVISED PER PCN-24-210586	10JUN2024	PS	CB
	F 1	REVISED PER PCN-24-223984	14OCT2024	RK	CB



SECTION A-A
WIRE BARREL


SECTION B-B

INSULATION BARREL

- 5 TIN PLATING MAY BE IN THIS REGION.
- 4 TIN PLATED REGION.
- 3 MATERIAL: .010 [0.25] THICK COPPER ALLOY.
- 2 WIRE RANGE: 22 AWG TO 16 AWG [0.35-1.50 mm²].
INSULATION RANGE: Ø.050-.085 [Ø1.27-2.16].
- 1 GOLD PLATED REGION.

NOTES: UNLESS OTHERWISE SPECIFIED

TE	INTERNAL PN	DEUTSCH PN	REV	PLATING
1060-20-0222	1060-20-0222	K	Ni/Cu Overall	
1060-20-0244	1060-20-0244	K	Selective Au, Ni/Cu Overall, Sn/Ni/Cu Wire Barrel	
1060-20-0277	1060-20-0277	K	Sn/Ni/Cu Overall	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 01DEC2009 J. APOSTOL CHK 02DEC2009 D. MEYER APVD 03DEC2009 R. REED		 TE Connectivity	
DIMENSIONS: INCHES[mm]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ±.025[0.64] 4 PLC ± ANGLES ±		NAME STAMPED CONTACT PIN SIZE 20	
		PRODUCT SPEC 108-151000 APPLICATION SPEC 114-151003			
MATERIAL 		FINISH - SEE TABLE		SIZE A3	CAGE CODE 4AFU8
		WEIGHT 0.15 g		DRAWING NO C-1060-20-02XX	
		CUSTOMER DRAWING		SCALE 6:1	SHEET 1 OF 1
				REV F1	