


TABLE 1	
MODEL NUMBER	LENGTH
415-0505-MM100	100mm ±6
415-0505-MM200	200mm ±6
415-0505-MM250	250mm ±6
415-0505-MM500	500mm ±6
415-0505-M1.0	1000mm ±12

REV	ECO	DATE
1	INITIAL RELEASE	04/24/2023
2	EC-2312006	12/12/2023
3	EC-2408008	08/15/2024



NOTES: UNLESS OTHERWISE SPECIFIED.

- 1. CABLE ASSEMBLY DIELECTRIC WITHSTANDING VOLTAGE: 500 VRMS FOR A PERIOD OF ONE MINUTE.
- 2. CABLE ASSEMBLIES TO BE 100% TESTED FOR VOLTAGE AND CONTINUITY.
- 3. ASSEMBLIES TO BE PACKAGED 1 PER BAG.
- 4. VSWR: 1.50 MAX DC-18GHz

PART LIST		
ITEM	QTY	DESCRIPTION
1	2	R/A SMP FEMALE
2	2 X1.00±.10	HEAT SHRINK TUBING
3	AR	CABLE



cinch
CONNECTIVITY SOLUTIONS
a bel group

This PROPRIETARY Document is property of Cinch Connectivity Solutions. It is confidential in nature, non-transferable, and issued with the clear understanding that it is not traced or copied without permission and is returnable upon demand.

INTERPRET DRAWING IN ACCORDANCE WITH ASME Y14.5-2018.

Model No: 415-0505-MXXXX

RoHS ☒ (EU)/2015/863 COMPLIANT

UNLESS OTHERWISE SPECIFIED
UNITS: INCH

.XX ± .01
.XXX ± .003
.XXXX ± .0010
ANGLE ± 2°

Cage Code 34078

3RD ANGLE PROJECTION

Drawn by: JIMMY CHEN

Date: 04/24/2023

JOHNSON

Title: CABLE ASSY. METRIC, R/A SMP FEMALE TO R/A SMP FEMALE, .086" FLEXIBLE

Drawing No. 415-0505-MXXXX

REV. 3

Size A DO NOT SCALE DRAWING

Workmanship Std: NONE

Sheet 1 OF 1