










REVISIONS					
REV	ECO	DESCRIPTION	DATE	BY	APPR
A1	--	RELEASED DRAWING	31/MAY/24	LUCAS	TOMMY



NOTES: UNLESS OTHERWISE SPECIFIED

- MATERIAL:
HOUSING: THERMOPLASTIC;
CONTACT: COPPER ALLOY, GOLD PLATING
SEAL: SILICONE RUBBER
- SPECIFICATIONS:
2.1 CURRENT RATING: 7.5AMPS MAX
2.2 OPERATING TEMPERATURE: -55°C TO +125°C
2.3 DIELECTRIC WITHSTANDING VOLTAGE: LESS THAN 2 MILLIAMPS CURRENT LEAKAGE @ 1500 VOLTS AC.
2.4 INSULATION RESISTANCE: 1000 MEGOHMS MIN @ 25°C.
2.5 MOISTURE RESISTANCE: IP67&IP69K (MATED CONDITION)
2.6 MATING CYCLE DURABILITY: 500 MIN CYCLES
2.7 RoHS COMPLIANT
- MATING PART: ATS06-34Sx2-* PLUG
(x = A,B KEYS ; * = ALL MODIFICATIONS)
- ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.



SEE P/N CHART		REF: 3-6437285-0, 3-6437285-1 (MATING INTERFACE ONLY)	
QUANTITY	PART NUMBER	DESCRIPTION	ITEM
MATERIALS LIST			
UNLESS OTHERWISE SPECIFIED 1) All dimensions are in metric(mm). 2) Tolerances are as follows: 1 PL DEC ±0.30 Fractions ±1/64 2 PL DEC ±0.15 Angles ±1° 3 PL DEC ±0.08 3) Note reference = 		SIGNATURES DATE DRAWN: LUCAS 31/MAY/24 CHECKED: ORION 03/JUN/24 ENGINEER: APPROVAL: TOMMY 05/JUN/24 CUSTOMER:	
MATERIAL SPECIFICATIONS:		34 POS, PCB RECEPT W/ FLANGE, PIN, ATS SERIES, W/ BOARDLOCK, PANEL, STRAIGHT, DOUBLE LATCH	
PROCESS SPECIFICATIONS:		THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.	
NEXT ASSY:		S1 SIZE B TYPE DWG NO. REVISION C-  ATS15-34Px2-BW01 A1	
		SCALE NONE	SHEET 1 OF 1

34 POS, PCB RECEPT W/ FLANGE, PIN, ATS SERIES, W/ BOARDLOCK, PANEL, STRAIGHT, DOUBLE LATCH