




ISS.	AMEND	DATE
1	ISSUED	10/12/15
2	PICTURE UPDATED	10/11/16
3	ADD M3 VARIANT	29/05/18



- Material:
1. Insert: ABS
 2. Frame: Nickel plated zinc diecast
 3. Shell: Nickel plated steel
 4. Contacts: Gold Plated

- Notes:
1. Voltage rating: 30V AC
 2. Current rating: 1.5 A max
 3. Contact resistance: 50m Ω max
 4. Insulation resistance: 20M Ω min
 5. Dielectric withstanding voltage: 500V AC
 6. Operating Temperature: -20°C to 50°C

VARIANTS	
PART No.	HOLE DETAILS
CP30209NM	HOLE $\varnothing 3.50$ x CSK 82° x $\varnothing 5.85$
CP30209NM3	M3 HOLES



RoHS COMPLIANT
TOLERANCE
NO DEC. PLACE \pm
1 DEC. PLACE \pm
2 DEC. PLACE \pm
HOLE \varnothing \pm
ANGLES \pm
UNLESS OTHERWISE STATED
DO NOT SCALE

Cliff Electronic Components Ltd.

76 Holmethorpe Avenue, Holmethorpe Industrial Estate,
Redhill, Surrey, RH1 2PF, England, UK
Tel: 01737-771375 Fax: 01737-766012 Website: www.cliffuk.co.uk

THE CONTENTS OF THIS DOCUMENT MUST NOT BE COPIED OR DISCLOSED
TO A 3rd PARTY WITHOUT WRITTEN PERMISSION OF CLIFF UK. © 2015

DIMENSIONS IN MILLIMETERS UNLESS OTHERWISE STATED. WORK TO DIMENSIONS. REMOVE ALL BURRS. IF IN DOUBT ASK.

3rd ANGLE PROJECTION:

MATERIAL: See Notes

FINISH: See Notes

DRAWN: D.P.J.

APPROVED: D.P.J.

TITLE: FT METAL USB 2.0 A to USB 2.0 B

DRWG. No. CP30209NM

FORM: A4DRWG