








END "A"
BARKLIP CONNECTOR (BK350 DRV3)

NOTES:


1. END "A" MATE WITH 6.00±0.20mm THICKNESS SILVER PLATING BUSBAR
2. ALL CABLE ASSEMBLIES SHALL 100% OPEN/SHORT TEST
3. SILVER PLATING CONTACT MAY DISCOLOR IN AIR, BUT NO PERFORMANCE ISSUE
4. AS LONG AS WIRE PIN ASSIGNMENT IS CORRECT, THE DIFFERENT COLOR CABLE LINE ON TOP OR BOTTOM CAN BE ACCEPTED. CROSS POINT POSITION IS ALSO NOT LIMITED.
5. MOUNTING HARDWARE:
3xM3 SCREWS
3x20mm dia. WASHERS
TORQUE SPEC: 0.4~0.6 N.M

spec ref				dr Andy Zhuang 2/13'23		Amphenol Power Solutions		MM		scale NA		size A3					
tolerance std				eng Andy Zhuang 2/13'23				ecr no									
TOLERANCES UNLESS OTHERWISE SPECIFIED				rvwr Siny Hu 2/13'23				rel level									
				appr Siny Hu 2/13'23		A Division of Amphenol Corporation amphenol-icc.com											
surface ✓		linear		projection		title BARKLIP CABLE ASSEMBLY		part no 10156914-1KP252LF		rev A		cat. no.					
												product family BK350 DRV3		Product - Customer Drw		sheet 1 of 2	
												0.X ±0.3		0.XX ±0.25		0.XXX ±	
		angular		0° ±		0° ±											



Dwg File: PHS-PUB-ACC-REV A J2023-07-13

BARKLIP CONNECTOR
(BK350 DRV3 IT Gear)

RECOMMENDED PANEL LAYOUT (BARKLIP CONNECTOR SIDE)






PE BAG


M3 SCREW
(STAINLESS STEEL)
RECOMMENDED TORQUE: 0.4~0.6 N.MWASHER (T=1.0mm Min)
(STAINLESS STEEL)

spec ref				dir Andy Zhuang 2/13'23		Amphenol Power Solutions		MM		scale NA		size A3			
tolerance std				eng Andy Zhuang 2/13'23				ecr no							
TOLERANCES UNLESS OTHERWISE SPECIFIED				rvwr Siny Hu 2/13'23											
				appr Siny Hu 2/13'23				A Division of Amphenol Corporation amphenol-tcc.com						rel level	
surface ✓		linear		0.X ±0.3		projection		title		BARKLIP CABLE ASSEMBLY		part no 10156914-1KP252LF		rev A	
				0.XX ±0.25											
		0.XXX ±													
angular		0° ±°				product family BK350 DRV3		Product - Customer Drw				sheet 2 of 2			

Dwg File: BARKLIP-PUR-100-REV A-2023-07-13

BARKLIP CONNECTOR
(BK350 DRV3 IT Gear)

RECOMMENDED PANEL LAYOUT (BARKLIP CONNECTOR SIDE)



PE BAG

M3 SCREW
(STAINLESS STEEL)
RECOMMENDED TORQUE: 0.4~0.6 N.M

WASHER (T=1.0mm Min)
(STAINLESS STEEL)

spec ref	dir	Andy Zhuang	2/13'23	Amphenol Power Solutions		MM	scale	size
tolerance sta	eng	Andy Zhuang	2/13'23			ecr no	NA	A3
TOLERANCES UNLESS OTHERWISE SPECIFIED	rvwr	Siny Hu	2/13'23			rel level		
	appr	Siny Hu	2/13'23					
surface	A Division of Amphenol Corporation			amphenol-icc.com		10156914-1KP252LF		
	product family			BK350 DRV3		Product - Customer Drw		
	sheet 2 of 2			cat. no.		rev		
	A			title		BARKLIP CABLE ASSEMBLY		

Dwg File: BARKLIP-PUR-100-REV A-2023-07-13