


NUMBER OF POSITIONS "n"	DIM "F"	DIM "G"
4	6.00	13.46
6	10.00	17.46
8	14.00	21.46
16	30.00	37.46

DC-BP REFERENCE



ISOMETRIC VIEW
SCALE 6/1






TABLE 4 10			
SCREW P/N	DESCRIPTION	BOARD THICKNESS	STACKING DISTANCE 4
809-0011-001	SCREW WITH WASHER, #0-80	3.5 to 5 mm	GREATER THAN 4.20
809-0011-002	SCREW WITH WASHER, #0-80	1.0 to 3.5MM	GREATER THAN 4.20
809-0016-000	SCREW WITH OUT WASHER, #0-80	1.0 to 3.5MM	STACKING DISTANCE FROM 4.00 TO 4.20
809-0017-000	SCREW WITH OUT WASHER, #0-80	3.5 to 5 mm	STACKING DISTANCE FROM 4.00 TO 4.20

TOLERANCES		DESIGN 07/12/2023 AC.PALLERI	Amphenol TCS A Division of Amphenol Corporation 200 Innovative Way, Nashua, NH 03062 603.879.3000	
0.0	±0.1	DRAWN 12/06/2023 AC.PALLERI		
0.00	±0.05	CHK 07/12/2023 D.SMITH	TITLE CUSTOMER USE DRAWING, RAF HD EXPRES, 4 PAIR	
0.000	±0.010	APVD 07/12/2023 D.SMITH	PART NO. SEE TABLE 1 - 3	REV N/A
ANGLES ±1°	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MM, DECIMAL MARKER IS A PERIOD		DRAWING NO. C-039-4100-500	REV F
CUSTOMER USE DRAWING		CREO ASSEM: 01252-FLP-BP-DC-CONNECTOR		0.2
		DRAWING: C-039-4100-500		0.7
SIZE D		SCALE 6/1	SHEET 2 OF 3	



INTERPRET PER ASME Y14.5M
CODE IDENT 31413

