









CKT. SIZE	DIM. A	DIM. B
6	.331 (8.40)	.543 (13.80)
8	.496 (12.60)	.709 (18.00)
10	.661 (16.80)	.874 (22.20)
12	.827 (21.00)	1.039 (26.40)
14	.992 (25.20)	1.205 (30.60)
16	1.157 (29.40)	1.370 (34.80)
18	1.323 (33.60)	1.535 (39.00)
20	1.488 (37.80)	1.701 (43.20)
22	1.654 (42.00)	1.866 (47.40)
24	1.819 (46.20)	2.031 (51.60)



- NOTES:
1. MATERIAL: BLANK=NYLON 6/6, UL 94V-2, COLOR: NATURAL
BL=NYLON 6/6, UL 94V-2, COLOR: BLACK
210=NYLON 6/6, UL 94V-0, COLOR: NATURAL
400=NYLON 6/6, UL 94V-0, COLOR: BLACK
 2. FINISH: N/A
 3. PRODUCT SPECIFICATION: PS-5556-001
 4. PACKAGING SPECIFICATION: PK-5559-002
 5. THIS PART MATES WITH RECEPTACLE #5557
 6. THIS PART IS FOR USE WITH MOLEX MALE TERMINAL #5558-*
 7. PART IS NOT DESIGNED FOR CURRENT SHARING
 8. CONNECTORS ARE NOT TO BE MATED OR UNMATED WHILE CIRCUITS ARE LIVE
 9. WIRES ARE TO BE DRESSED IN SUCH A MANNER TO ALLOW THE TERMINALS TO FLOAT FREELY IN THE POCKET
 10. PART CONFORMS TO CLASS "B" REQUIREMENTS OF COSMETIC SPECIFICATION PS-45499-002 WITH THE EXCEPTION OF DISCOLORATION. FLASH AND SINK MEET CLASS "C" REQUIREMENTS.

OBS -220 P/NS EC NO: UCP2015-4965 2015/05/26 DRWN:JONTI CHKD:JBELL APPR:FSMITH 2015/06/17	DESCRIPTION REV	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE 4:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION			
				mm	INCH	DRAWN BY RJF	DATE 1989/09/22	TITLE MINI FIT JR SERIES PLUG W/O MTG. EARS				
			4 PLACES	± .005	± .005	CHECKED BY BAP	DATE 1989/09/22					
			3 PLACES	± .005	± .015	APPROVED BY ROS	DATE 1989/09/22					
			2 PLACES	± 0.38	± .005	MATERIAL NO.		DOCUMENT NO. SD-5559-NP1*				
			1 PLACE	± .005	± .005	SIZE C						
			ANGULAR ±1/2°		SEE CHART							
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS									

